







未注公差/General tolerances (mm)

0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	>500	0.1/10
~3	~6	~10	~18	~30	~50	~80	~120	~180	~250	~315	~400	~500	~500	±2°
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	

please refer to the 3D model,
for those unmarked dimensions.



1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES
使用温度范围/Operating temperature(°C)			-40~+105
符合RoHS环保要求/Conform to RoHS			Yes

		MATERIAL: PA66		SURFACE/COLOR:	
APPD: 蓝黄凡		MAT NO./REV: -		MAT STATUS: 批量	
CHKD: 曹利彬		NAME: DGBSC-ACC01-11-00Z(H)			
DFT: 姜民洁		DRAWING NO.	TYPE	DRAWING STATUS	SCALE
2023.11.09		200198092	CUSTOMER DRAWING	已发布	2:1
					SHEET
					1/1

00	ECN	DESCRIPTION	DFT	DATE
REV				