

Transfer or duplication of this document, as well as the utilization of its contents without the prior written authorization of DEGSON, shall be held responsible. All rights reserved for patent. 未經許可，不得複製、轉售或將本文件內容用於其他用途。所有權利均受專利保護。

FOR-1759 Rev.2.3






品名/Name	按钮颜色/The button color	塑件&盖板颜色/The housing&cover color
DGBSC-SG01/4-XXP (1Y-00AH) DGBSC-SG01/4-XXP (1Y-00ZH)	绿色/Green	透明/Transparent
DGBSC-SG01/4-XXP (1Y-01AH) DGBSC-SG01/4-XXP (1Y-01ZH)	白色/White	透明/Transparent
DGBSC-SG01/4-XXP (1Y-10AH) DGBSC-SG01/4-XXP (1Y-10ZH)	绿色/Green	透明/Transparent
DGBSC-SG01/4-XXP (1Y-11AH) DGBSC-SG01/4-XXP (1Y-11ZH)	棕色/Brown	透明/Transparent
DGBSC-SG01/4-XXP (1Y-12AH) DGBSC-SG01/4-XXP (1Y-12ZH)	蓝色/Blue	透明/Transparent
DGBSC-SG01/4-XXP (1Y-13AH) DGBSC-SG01/4-XXP (1Y-13ZH)	黑色/Black	透明/Transparent
DGBSC-SG01/4-XXP (17-14AH) DGBSC-SG01/4-XXP (17-14ZH)	绿色/Green	透明黄/Yellow Transparent
DGBSC-SG01/4-XXP (1Y-15AH) DGBSC-SG01/4-XXP (1Y-15ZH)	红色/Red	透明/Transparent
DGBSC-SG01/4-XXP (17-16AH) DGBSC-SG01/4-XXP (17-16ZH)	绿色/Green	透明/Transparent
DGBSC-SG01/4-XXP (1Y-17AH) DGBSC-SG01/4-XXP (1Y-17ZH)	绿色/Green	透明/Transparent
DGBSC-SG01/4-XXP (17-24AH) DGBSC-SG01/4-XXP (17-24ZH)	霓虹黄绿/Yellow and Green	透明/Transparent
DGBSC-SG01/4-XXP (17-25AH) DGBSC-SG01/4-XXP (17-25ZH)	黄色/Yellow	透明/Transparent
DGBSC-SG01/4-XXP (17-26AH) DGBSC-SG01/4-XXP (17-26ZH)	绿色/Green (Pantone 5473C)	透明/Transparent
DGBSC-SG01/4-XXP (17-28AH) DGBSC-SG01/4-XXP (17-28ZH)	橙色/Orange (Pantone 15051)	透明/Transparent
DGBSC-SG01/4-XXP (17-63AH) DGBSC-SG01/4-XXP (17-63ZH)	红色/Red (Pantone 485C)	透明/Transparent
DGBSC-SG01/4-XXP (1Y-304ZH)	蓝色/Blue	透明/Transparent
DGBSC-SG01/4-XXP (1Y-305ZH)	棕色/Brown	透明/Transparent
DGBSC-SG01/4-XXP (1Y-306ZH)	黑色/Black	透明/Transparent

● Differentiation from-00A:Different packing methods.
10AZ for boxed packaging


● Differentiation from-00A:Different packing methods.
16AZ is in bag packing&papercard packing

● Differentiation from-00A:Different packing methods.
25AZ for boxed packaging

● Differentiation from-00A:Different packing methods.
304/305/306 Z is in bag packing&papercard packing



The test hole at 02P is on the right



Please refer to the 3D model for those unmarked dimensions

7 公差/General tolerances(mm)													8 公差/General tolerances(mm)		
0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	>500	0.1/10	±2
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±1.05	±1.15	±1.60	±2.20	±2.50	±2.50	±2	±2
UL 标准/UL Standard:													600		
IEC 标准/IEC Standard:													III/3		
过压类别/Overvoltage Category/污染等级/Pollution Degree													III/2		
额定电压/电压/Rated Voltage(V)/Current(A)													450/32		
工频耐压/Withstanding voltage(V/1Min)													AC2500		
线径范围(硬线和软线)/Wire Range(rigid and flexible)(AW)													24~12 / 0.2~4.0		
间距/Pitch(mm)/线数范围/Poles													5.6N=02P/03P/05P		
剥线长度/Stripping length(mm)													12		
使用温度范围/Operating temperature(°C)													-40~+85 (IEC)		
符合RoHS环保要求/Conform to RoHS													Yes		
Mark DGBSC-SG01/4-02P; 600V Cu													24-12AWG sol&str		
5	Current carrier			Copper			Sn Plated								
4	Spring			Stainless steel			/								
3	Button			PA66+GF			UL94V-0								
2	Cover			PC			UL94V-2								
1	Housing			PC			UL94V-2								
ITEM	NAME OF PART			MATERIAL			NOTES								

03	ECN	DESCRIPTION	版本正	2025.11.13	DRFT	DATE	A3	200066324	CUSTOMER DRAWING	已发布	SCALE	1:1	SHEET	1/4
----	-----	-------------	-----	------------	------	------	----	-----------	------------------	-----	-------	-----	-------	-----

DEGSON		MATERIAL:		SURFACE/COLOR:	
APPD: 黄耀志		MAT NO./REV:		MAT STATUS: work	
CHKD: 朱岳鹏		NAME:		DGBSC-SG01/4-XXP (1Y-306ZH)	
DRFT: 黄耀正		DRAWING NO.		TYPE	
		200066324		CUSTOMER DRAWING	
		DRAWING STATUS		SCALE	
		已发布		1:1	
		SHEET		1/4	