

2 in 1 –
Hair and beard trimmer

Housing with scratch-
resistant chrome inlay

Precision shaving head
with high quality
stainless steel blade

Quick charge function
(60 min.)

Battery operation



2ⁱⁿ₁



Hair and beard trimmer

Hair and beard trimmer HSM/R 3827

Without decoration

- 2 in 1 - Hair and beard trimmer with scratch-resistant chrome insert
- Also ideal as a body hair trimmer for trimming, styling and shaving facial and body hair
- Battery operation
- Quick charge function (60 min.)
- Battery life: up to 100 min.
- Precision shaving head with high-quality stainless steel blade
- 16 cutting lengths possible (1 - 30 mm)
- 2 removable comb attachments for 16 cutting lengths (1-15 mm, 16-30 mm)
- Easy handling thanks to non-slip handle
- Housing with scratch-resistant chrome inlay
- Detachable shaving head for easy cleaning
- Incl. 4-piece accessories: USB-C charging cable, cleaning brush, 2 comb attachments (1-15 mm, 16-30 mm)
- Lithium ion battery; 3.7 V; 600 mAh; 18,6 g

16

Cutting lengths
possible
(1 - 30 mm)



Standard
USB-C charging port



Removable comb
attachment (1 - 15 mm)



Precision shaving head
with high quality
stainless steel blade



Removable comb
attachment (16 - 30 mm)

Colour: chrome-black
Article no.: 264 049
Article EAN-Code: 4 006 160 640 496
Exportpack EAN-Code: 4 006 160 019 766

PU: 6
20"/40"/HQ container: 21552 / 43110 / 50166

Dimensions: (approx. W x H x D)
Unit: 45 x 175 x 35 mm
Box: 100 x 185 x 60 mm

CTC **CLATRONIC®**
CTC Clatronic International GmbH
Industriering Ost 40
47906 Kempen