

HP 5" Touch Screen Film Scanner

Enjoy The View with a Larger LCD Screen

It's easy to see why this scanner's large, clear LCD screen makes viewing images a pleasure. Scan color and B&W negatives (135, 110, 126) and 50 mm slides (135, 110, 126) to preserve precious memories digitally and keep them for years to come.



Film negatives



50mm slides



Touchscreen Display



Transfer to Computer

HPFS500
UPC: 198869003475

Specs

IMAGE SENSOR:	13 megapixels color CMOS sensor
DISPLAY:	5" all-angle color LCD
LENS SPECIFICATION:	F/No. 3.5, 7-element lens
COLOR BALANCE:	Automatic
EXPOSURE CONTROL:	Automatic/Manual
SUPPORTED FILM TYPES:	Slide/negative film (135, 110, & 126)
PICTURE FORMATS:	Black & white, slides, negatives
FOCUS:	Fixed
EV ADJUSTMENT:	Yes, +/- 2.0 EV

RGB COLOR ADJUSTMENT:	Yes
CONTRAST ADJUSTMENT:	Yes
PC INTERFACE:	USB 2.0
IMAGE FORMAT:	135/3:2, 110/4:3, 126/1:1
POWER SUPPLY:	From PC USB port, external 5V USB port
LIGHT SOURCE:	White LED panel
USB CONNECTOR:	Type-C
DIMENSIONS:	4.66" x 5.7" x 3.54" (118.5 x 145 x 90 mm)



HP 5" Touch Screen Film Scanner

Package contents

Touch screen film adapter
50 x 50 mm hinged slide holder
110 film adapter
126 film adapter
135 film adapter
USB cable
Cleaning brush
User manual

SKU

HPFS500

UPC

198869003475



5" Full-color
Touchscreen Display



Automatic Cropping
and Manual Adjustment




13-megapixel
CMOS Sensor



Adjust Brightness,
Contrast, and Color



Transfer to
Computer



Film Negatives
and 50mm Slides



Visit us at: www.hpdevices.com
Contact: support@hpdevices.com



HP is a trademark of HP Inc. or its affiliates, used by C&A Marketing, Inc. under license from HP Inc.

SD is a trademark of SD-3C, LLC.

All other products, brand names, company names, and logos are trademarks of their respective owners, used merely to identify their respective products, and are not meant to connote any sponsorship, endorsement, or approval.

Distributed by C&A Marketing, Inc. under license from HP Inc. 114 Tived Lane East, Edison, NJ 08837.

© 2025. All Rights Reserved. Made in China.