

KODAK LUMA 500

FHD ULTRA SMART PICO PROJECTOR



MINI PROJECTOR. MEGA POWER.




PLAY IT SMART

With Google TV™ 11.0 OS, this smart projector ensures seamless access to movies, TV shows, and more. Connect to Chromecast built-in or choose from 400K+ apps available on Google Play, and navigate hands-free with the voice-activated Google Assistant remote.



KEEP THINGS CRYSTAL CLEAR

Immerse yourself in stunning visuals with 1920x1080p full HD native resolution, HDR and 4K support. With DLP 0.23 technology, this compact smart projector delivers the perfect picture, anytime, anywhere.



ANY WAY YOU VIEW IT

More than just a streaming device, the Kodak Luma 500 is the ultimate projection tool for crafts, business presentations, classrooms, and more. Project a design and trace it onto a mural, deliver an impactful presentation, or keep your students engaged - take advantage of the projector's incredible versatility!



TAKE IT ON THE GO

The lightweight Kodak Luma 500 is your versatile, travel-sized companion for an exceptional viewing experience anywhere you go. With a built-in 2-hour battery life on eco mode, Bluetooth and Wi-Fi connectivity, and built-in HDMI and USB input, taking advantage of this compact projector's on-the-go connectivity is a breeze.



BRING ON THE BIG SCREEN

Enjoy vibrant, lifelike colors and take in the visual beauty of full RGB LED color. With a 30,000 hour LED life and 150 ANSI lumens, your media stays perfectly illuminated while projecting on screens as small as 10 inches and as large as 150"!



PERFECTLY ADJUSTED TO YOU

Easily adjust to the perfect picture with auto-focus and multiple projection modes. Featuring auto keystone & manual 4-point correction and 100% offset, this mini smart projector gets all the right angles, every time. Connect it to the included tripod and get ready to enjoy.



Black: RODPJS500B



White: RODPJS500

KODAK LUMA 500

FHD ULTRA SMART PICO PROJECTOR

SPECIFICATIONS

Package Includes	• Kodak Luma 500 FHD Ultra Smart Pico Projector • DC 15V/2.4A power adapter • US, EU, and UK plugs • Voice-enabled Bluetooth remote control	• AAA battery x2 • QSG • Tripod
Display	• Display Technology: DLP 0.23" DMD • Light Source: RGB LED • Lamp Life: 30000 hours • Brightness: 150 ANSI lumens	• Supported Format: HDR+ • Native Resolution: 1920 x 1080p • Supported Resolution: 4K • Light Uniformity: ≥ 90%
Projector	• Throw Ratio: 1.2:1 • Lens Focus Mode: Autofocus & manual electrical on HW + remote • Zoom: 50% - 100% • Screen Size: 10" - 150" • Contrast Ratio: 400:1 (2000:1 dynamic) • Keystone: Auto keystone, manual 4 point correction ± 40 degrees • Offset: 100% • Projection Mode: Front, front ceiling, rear, rear ceiling • Touch-sensitive controls	
Sound	• Speaker: 1.5W x 2 • Dolby® & Dolby Digital Plus™ support	
System	• SoC: MT9630 • CPU: Quad core ARM Cortex-A53 CPU • GPU: G52MC1	• OS: Google TV™ 11.0 • RAM: 2 GB • ROM: 16 GB
Input	• USB: USB 2.0 • HDMI®: HDMI 2.1	• HDCP: HDCP 2.2/1.4 compliant
Wireless	• Wi-Fi: 802.11a/b/g/n/ac dual frequency 2.4/5GHz • Wireless Input: Chromecast	• Bluetooth: Bluetooth 5.0
Power	• Power Input: DC 15V/2.4A • Noise Level in dB: 30dB • Operation Temperature: 5-35 °C	• Power Consumption Rate: 36W • Standby Power Consumption: 0.5 • Battery: Built-in battery 10500mAh
Product	• Dimensions: 5.2" x 5.2" x 1.3" (132 x 132 x 34 mm) • Weight: 1.275 lb. (570g)	
Packaging	• Gift box • Box size: 7.48" x 6.3" x 3.543" (190x 160 x 90 mm) • Boxes per carton: 8 (units)	• Carton size: 15" x 13.39" x 8.27" (380 x 340 x 210 mm) • Carton gross weight: 23.15 lb. (10.5 kg)
MODEL/UPC#	White: RODPJS500/ UPC#: 843812189972 Black: RODPJS500B/UPC#: 843812189989	
Certificates	FCC, CE, REACH, RoHS, Prop 65	

kodakphotoplus.com

The Kodak trademark, logo, and trade dress are used under license from Eastman Kodak Company.

The Kodak trademark, logo and trade dress are used under license from Kodak.

HDMI, the HDMI logo, and High-Definition Multimedia Interface are trademarks or registered trademarks of HDMI Licensing, LLC in the United States and/or other countries.

Bluetooth is a trademark of Bluetooth SIG, Inc. USA.

Wi-Fi is a trademark of Wi-Fi Alliance in the US and/or other countries.

Google TV is the name of this device's software experience and a trademark of Google LLC. Chromecast built-in and Google Play are trademarks of Google LLC.

Netflix is a registered trademark of Netflix, Inc.

DLP® and the DLP logo are registered trademarks of Texas Instruments.

Dolby and Dolby Digital Plus are trademarks or registered trademarks of Dolby Laboratories.

All other products, brand names, company names, and logos are trademarks of their respective owners, used merely to identify their respective products, and are not meant to connote any sponsorship, endorsement, or approval.

Distributed by: C&A Marketing, Inc., 114 Tived Lane East, Edison, NJ 08837 USA

© 2023. C&A IP Holdings, LLC. All Rights Reserved. Made in the USA.

