

4X4 BOX 7000/D5 Series

4X4 BOX-7735U/D5, 4X4 BOX-7535U/D5

Fanned BOX



KEY FEATURES

- AMD Ryzen™ 7000U-Series
- 2 x 262-pin SO-DIMM DDR5 4800MHz up to 64GB (32GB per DIMM)
- 2 x USB4, 1 x USB 3.2 Gen2, 2 x USB 2.0, 1 x M.2 Key M, 1 x M.2 Key E (WiFi-6E Module), 1 x SATA3
- 1 x Realtek 1 Gigabit LAN, 1 x Realtek 2.5 Gigabit LAN
- Supports Quad display, 1 x HDMI 2.1, 3 x DP 1.4a (2 from Type-C)
- TPM 2.0 onboard IC
- 19V, 120/90W Power Adapter
- 117.5 x 110.0 x 47.85mm(4.63" x 4.33" x 1.88"), Fanned Barebone

SPECIFICATIONS

Processor System

CPU	AMD Ryzen™ 7000U-Series 4X4 BOX-7735U/D5 (AMD Ryzen™ 7 7735U, 8Cores, Max Speed up to 4.75GHz) 4X4 BOX-7535U/D5 (AMD Ryzen™ 5 7535U, 6Cores, Max Speed up to 4.55GHz)
Chipset	SoC
BIOS	AMI SPI 256 Mbit

Memory

Technology	Dual Channel DDR5 4800 MHz
Capacity	64GB (32 GB per DIMM)
Socket	2 x 262-pin SO-DIMM

Graphics

Controller	AMD Radeon™ Graphics
HDMI	HDMI 2.1 Max resolution up to 7680 x 4320@60Hz
DisplayPort	DisplayPort 1.4a, DP++ Max resolution up to 4096x2160@60Hz
MultiDisplay	Max 4 display (Included 2 outputs from Type-C)

Expansion Slot

M.2/WLAN	1 x Wi-Fi 6E 802.11ax + BT 5.2
----------	--------------------------------

Audio

Interface	Realtek ALC233, High Definition Audio.
-----------	--

Ethernet

Controller/ Speed	LAN1: Realtek RTL8125BG with 10/100/1000/2500 Mbps LAN2: Realtek RTL8111EPV with 10/100/1000 Mbps, support DASH function
Connector	2 x RJ-45

Storage

M.2	1 x M.2 (Key M, 2242/2260/2280) with PCIe Gen4 x4 for SSD *M.2 Key M 2280(Supported by bracket)
SATA	1 x SATA3.0 (6.0 Gb/s)

Front I/O

USB	1 x USB 3.2 Gen2 (Type-A) 2 x USB4 (Supports DP1.4a display output)
Audio	1 (headphone & microphone jack)

Rear I/O

HDMI	1 x HDMI 2.1
DisplayPort	1 x DP1.4a
Ethernet	1 x 1 Gigabit LAN, 1 x 2.5 Gigabit LAN
USB	2 x USB 2.0
DC Jack	1

Watchdog Timer

Output Interval	From Super I/O to drag RESETCON# 256 Segments, 0, 1, 2, ...255sec
-----------------	--

Power Requirements

Input PWR Power On	12V~19V DC-In Jack AT/ATX Supported - AT : Directly PWR on as power input ready - ATX : Press button to PWR on after power input ready
--------------------	---

Environment

Operating Temp	0°C ~ 40°C
Storage Temp	-40° C ~ 85° C
Operating Humidity	5% ~ 90%
Storage Humidity	5% ~ 90%

Mechanical

Mounting	VESA mount
Dimensions (L x W x H)	117.5 x 110.0 x 47.85mm(4.63" x 4.33" x 1.88")
Weight	Net Weight: 1kg

Others

OS Support	Windows 10/11
TPM	TPM 2.0 onboard IC
Certifications	CE, FCC
Packing List	19V/120W Power Adapter (R7 7735U) 19V/90W Power Adapter (R5 7535U) 1 x VESA mount bracket