

VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

MLSet-100 **CAT III 1000 V TEST LEADS SET**

CE

Item no. 3730549



PACKAGE CONTENTS

- 2x Test probe extenders
- 2x Alligator clips
- 2x Test probes
- 2x IC hook type test clips
- 2x IC crocodile clip test clips
- 2x Safety test clips
- 2x Test leads
- Bag



TECHNICAL DATA

General

Item	Value
Working temperature and humidity	-5 to +45 °C / <85 % RH
Storage temperature and humidity	-10 to +50 °C / <85 % RH
Colors	Red, black

Test probe extenders

Item	Value
Overvoltage category	CAT III 1000 V
Rated current	max. 10 A
Connector	4 mm
Material	TPE + PP
Length	208.5 mm

Alligator clip

Item	Value
Overvoltage category	CAT III 1000 V / CAT IV 600 V
Rated current	max. 10 A
Connector	4 mm
Material	PP + PA

Test probes

Item	Value
Overvoltage category	CAT III 1000 V / CAT IV 600 V
Rated current	max. 10 A
Connector	4 mm
Material	TPE + PP

IC hook type test clips

Item	Value
Overvoltage category	CAT III 1000 V / CAT IV 600 V
Rated current	5 A
Connector	4 mm
Plug shape	Angled
Material	PA

IC crocodile clip test clips

Item	Value
Overvoltage category	CAT III 1000 V / CAT IV 600 V
Rated current	5 A
Connector	4 mm
Plug shape	Angled
Material	PP + PA

Safety test clip

Item	Value
Overvoltage category	CAT III 1000 V / CAT IV 600 V
Rated current	max. 5 A
Connector	4 mm
Plug shape	Angled
Material	PA

Test leads

Item	Value
Overvoltage category	CAT III 1000 V / CAT IV 600 V
Rated current	max. 10 A
Connector	4 mm
Plug shape	Straight, Angle
Material	PVC, nickel-plated
Cable length	1.2 m