

VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

MLSet-120 CAT III 1000 V TEST LEADS SET

CE

Item no. 3730550



PACKAGE CONTENTS

- 2x Test leads
- 2x Test leads (grip clamp)
- 2x Test leads (IC clip)
- 2x Test probes
- 2x Test leads (banana plug)
- 2x Adapter plugs
- 2x Test clips
- 2x Test probes
- Bag



TECHNICAL DATA

General

Item	Value
Working temperature and humidity	-5 to +45 °C / <85 % RH
Storage temperature and humidity	-10 to +50 °C / <85 % RH
Colors	Red, black

Test leads

Item	Value
Overvoltage category	CAT III 1000 V / CAT IV 600 V
Rated current	max. 10 A
Connector	4 mm
Plug shape	Straight, Angle
Material	PVC, nickel-plated
Cable length	1.2 m

Test leads (grip clamp)

Item	Value
Overvoltage category	CAT II 300 V
Rated current	3 A
Connector	4 mm
Plug shape	Straight
Plug type	Grip clamp
Material	PA
Cable length	1.2 m

Test leads (IC clip)

Item	Value
Overvoltage category	CAT II 300 V
Rated current	3 A
Connector	4 mm
Plug shape	Straight
Material	PA
Cable length	1.2 m

Test probes

Item	Value
Overvoltage category	CAT III 1000 V / CAT IV 600 V
Rated current	max. 10 A
Connector	4 mm
Material	TPE + PP

Test leads (banana plug)

Item	Value
Overvoltage category	CAT I 30VAC / 60VDC
Rated current	3 A
Connector	4 mm
Plug type	Banana plug to 0.64 mm rectangular socket
Plug shape	Straight
Material	PVC / PA
Cable length	1 m

Adapter plugs

Item	Value
Overvoltage category	CAT III 1000V / CAT IV 600V
Rated current	10 A
Connector	4 mm
Plug shape	Straight
Material	PP
Length	69 mm

Test clips

Item	Value
Overvoltage category	CAT II 1000 V
Rated current	5 A
Connector	4 mm
Plug shape	Straight
Material	PA

Test probes

Item	Value
Overvoltage category	CAT IV 600V / CAT III 1000V
Rated current	10 A
Connector	4 mm
Plug shape	Straight
Material	TPE + PP