



# DEEBOT T90 PRO OMNI

The Robotic Vacuum Cleaner Engineered for **Perpetual Cleaning Power**





# DEEBOT T90 PRO OMNI

Simple by Design. Powerful in Action



## OZMO ROLLER 3.0 with TruEdge

*Power the Wash. Accelerate the Clean.*

OZMO ROLLER 3.0 Instant Self-Washing Mopping is now 50% longer at 27 cm, offering wider, more efficient coverage. Powered by a high-performance air pump, its pressurized self-washing system releases energetic water pulses through 32-way precision nozzles. During operation, the mop spins at up to 200 RPM to maintain consistent cleanliness and prevent streaks or secondary contamination. Combined with strong downward pressure, it delivers a deep, even clean that dries quickly—keeping your floors spotless with zero effort.

The upgraded TruEdge 3.0 Extreme Edge Cleaning technology with new air-felt protection allows DEEBOT to glide and clean along baseboards like a whisper while safeguarding your furniture from scratches.



## PowerBoost Charging

*Perpetual Run. Unstoppable Clean.*

DEEBOT T90 PRO OMNI's revolutionary PowerBoost Technology transforms your cleaning experience through ultra-fast energy boosts and non-stop cleaning freedom. Its self-optimizing algorithm dynamically reserves power to prioritize full-space completion, while the PowerBoost Technology restores 10% battery power in 3 min during routine mop cleaning intervals.

As a result, DEEBOT T90 PRO OMNI enables an intelligence-driven perpetual run for truly uninterrupted cleaning coverage up to 500m<sup>2</sup> per task, even at max settings, ensuring consistent performance across large areas without worrying about limited power battery.



## ZeroTangle 4.0 Empowered by BLAST

*BLAST Away the Tangle. Clear Off the Clutter.*

The all-new Airflow-Directed Anti-Tangle Main Brush redefines cleaning with its Airflow-Directed Anti-Tangle System, featuring exclusive lateral airflow channel empowered by BLAST, the powerful large-airflow suction technology that unleashes 16L/s airflow, to efficiently draw in dust and capture every strand of hair—smoothly and completely tangle-free.

Supported by a reinforced, wide-span dual-bearing structure, it delivers stable, quiet, yet powerful scrubbing performance for a cleaner, more effortless experience.



## All-Dimensional Noise Reduction

*Clean Beyond Quietness.*

Through comprehensive redesigns and optimizations to the main brush, fan, and air-duct structure, DEEBOT achieves a remarkable reduction in operating noise—by up to 3 dBA during dust collection and 5 dBA during suction. This corresponds to a reduction in noise intensity of approximately 50% and 68%, respectively.

The result is a noticeably quieter clean that enhances everyday comfort while unlocking the full potential of Boosted Large-Airflow Suction Technology (BLAST)—delivering powerful, high-efficiency suction that's strong yet remarkably unobtrusive, so you can clean with confidence and without disruption.



## TruePass Adaptive 4-Wheel-Drive Climbing System

*Access All Areas Seamlessly.*

The TruePass Adaptive 4-Wheel-Drive Climbing System adopts an innovative mechanical climbing system to guarantee a reliable crossing over most household thresholds. When facing impassable obstacles, the robot instantly deploys two auxiliary levering wheels. Their soft rubber gripping teeth can firmly latch onto surfaces—dramatically boosting climbing ability to handle a single stage up to 2.4cm height and continuous stages up to 4cm height.

Unlike vision-based systems, this purely mechanical mechanism activates immediately upon contact, ensuring flawless, on-time engagement and eliminating missed or failed climbing attempts for truly seamless cleaning.



# DEEBOT T90 PRO OMNI

## Key Technologies

### Cleanliness

- OZMO ROLLER 3.0 - 50% Longer Mop Roller with Pressurized Self-Washing
- TruEdge 3.0 Extreme Edge Cleaning
- BLAST + 30.000 Pa
- ZeroTangle 4.0 Airflow-directed Anti-tangle Technology
- Fresh Flow Power Washing + Dirty Water Auto Emptying
- 15mm Mop Lifting

### Intelligence

- AGENT YIKO with upgraded Pet Care

### Mobility

- TruePass Adaptive 4WD Climbing System
- AIVI 3D 4.0 – Approach or Distance Strategy

### Convenience

- PowerBoost Charging
- All-Dimensional Noise Reduction
- 95mm ultra-thin body
- Minimalist and refined aesthetic
- Mobile App with Easy Mode

## ID Pictures



## Specification

### DEEBOT T90 PRO OMNI BLACK EU

|                                         |                                                           |
|-----------------------------------------|-----------------------------------------------------------|
| Battery                                 | Li-Ion, 4000 mAh Super Boost                              |
| SRP                                     | 799€                                                      |
| Charging Time                           | 2h 30min                                                  |
| Dimension with product packaging        | 56 * 38 * 40.8 cm                                         |
| Dimension of Robot                      | 35.3 * 35.1 * 9.5 cm                                      |
| Dimension of Station                    | 33.8 * 46 * 50 cm                                         |
| Dust Bag (Station)                      | 2.5                                                       |
| Dust Container                          | 250 ml                                                    |
| Navigation Type                         | Mini-ToF                                                  |
| Noise level Robot (vacuum & mop)        | 60                                                        |
| Obstacle Avoidance                      | AIVI 3D 4.0: Structured light, RGB AI+Supplementary Light |
| Runtime (Vacuum & Mop) Standard suction | 350 min                                                   |
| Suction Power                           | 30000Pa, 16 L/s                                           |
| Watertank size – Station                | 4(clean)/2,2(dirty)                                       |
| Watertank size – Robot                  | 110ml                                                     |
| Working voltage (V) Robot               | 16.6V                                                     |
| Rated Power (W) Robot                   | 65W                                                       |
| Weight w/o packaging kg                 | 14.46                                                     |
| Weight Net Kg                           | 13.2                                                      |
| Weight with product packaging kg        | 17.73                                                     |
| EAN                                     | 6970135039418                                             |

## What is in the box?

|                                     |   |
|-------------------------------------|---|
| Robot (pcs)                         | 1 |
| OMNI Cyclone Station                | 1 |
| Power cord (pcs)                    | 1 |
| User Manual (pcs)                   | 1 |
| Quick guide (pcs)                   | 1 |
| Replaceable Long roller mop (pcs)   | 1 |
| Side brush (pcs)                    | 1 |
| Main brush & Main Brush Cover (pcs) | 1 |
| Antibacterial Dust Bag (pcs)        | 1 |
| Antibacterial Filter (pcs)          | 1 |
| Clean water tank (pcs)              | 1 |
| Dirty water tank (pcs)              | 1 |
| Deebot Cleaning Solution 260ml      | 1 |