

Portable Compressor Cooler 19L

- Strong compressor technology
- Durable design and quiet operation (less than 45dB)
- Adjustable cooling mode:
Fast cooling / Energy saving
- Built-In car battery protection
- Control by ProUser Power App



CoolZ 19

Name		Pro-User CoolZ 19
Art.no.		20409
EAN		8717809204097
Net. capacity		19 liters

Electrical	
Input voltage	220V - 240V
Input DC voltage	12V / 24V
Power consumption	45W
Input AC current	0.20A
Input DC current	3.75 / 1.88A

Performance	
Classification climate	T / ST / N
Refrigerant	R600a
Cooling system	Compressor
Temperature range	-20°C - +20°C
Noise level	< 45dB

Measurements	
Dimensions	L513 x W349 x D424 mm
Weight	8.9 kg
Package dimensions	L548 x W396 x H484 mm
Package weight	10.8 kg

Included	
• 230V and 12V adapter	• Built-in LED light inside
• Removable wire rack	• Cutting board
• Bottle opener	• Fitting cooling bag

Available accessories	
Stand	20439
Powerbank	20414



Portable Compressor Cooler
CoolZ 19

PRO ELECTRONICS®
USER