

Portable Compressor Cooler 65L

- Strong compressor technology
- Durable design and quiet operation (less than 45dB)
- Adjustable cooling mode:
Fast cooling / Energy saving
- Built-In car battery protection
- Control by ProUser Power App



CoolZ 65

Name		Pro-User CoolZ 65
Art.no.		20412
EAN		8717809204127
Net. capacity		65 liters

Electrical	
Input voltage	220V - 240V
Input DC voltage	12V / 24V
Power consumption	60W
Input AC current	0.26A
Input DC current	5 / 2.5A

Performance	
Classification climate	T / ST / N
Refrigerant	R600a
Cooling system	Compressor
Temperature range	-20°C - +20°C
Noise level	< 45dB

Measurements	
Dimensions	L775 x W441 x D477 mm
Weight	16.9 kg
Package dimensions	L798 x W508 x H536 mm
Package weight	19.7 kg

Included	
• 230V and 12V adapter	• Built-in LED light inside
• Removable wire rack	• Cutting board
• Bottle opener	• Fitting cooling bag

Available accessories	
Stand	20439
Powerbank	20414



Portable Compressor Cooler
CoolZ 65

PRO ELECTRONICS®
USER