

TECHNICAL DATA

Fluke AC385 / AC385-RGB SureGrip™ Alligator Clip Sets, CAT III 1500 V / CAT IV 1000 V, 30A



Key features

- Rated CAT III 1500 V / CAT IV 1000 V, 30A for use in high-voltage environments
- Nickel-plated steel jaws for durable, secure connections
- SureGrip™ design improves handling and grip in the field
- Wide jaw opening accommodates large terminals and conductors

Product overview: Fluke AC385 / AC385-RGB SureGrip™ Alligator Clip Sets, CAT III 1500 V / CAT IV 1000 V, 30A

The Fluke AC385 and AC385-RGB SureGrip™ Alligator Clip Sets are built to deliver strong and safe connections in solar and high-voltage testing environments. Both models meet CAT III 1500 V and CAT IV 1000 V, 30A safety ratings. The rugged nickel-plated jaws ensure reliable contact with conductors, while the ergonomic SureGrip™ design provides superior control even in challenging conditions. The AC385-RGB model includes 3 color-coded clips to support solar ground fault testing workflows, compatible with TL324-RGB test leads.

Specifications: Fluke AC385 / AC385-RGB SureGrip™ Alligator Clip Sets, CAT III 1500 V / CAT IV 1000 V, 30A

- Safety Rating: CAT III 1500 V / CAT IV 1000 V, 30A
- Jaw Opening: Up to 36.7 mm (1.44 in)
- Connector Type: 4 mm shrouded banana plug
- Operating Temperature: -20 °C to 50 °C (-4 °F to 122 °F), 95% RH
- Pollution Degree: 2
- Altitude: Up to 3000 m

Ordering information



AC385

AC385 SureGrip™ Alligator Clip Set, CAT III 1500 V / CAT IV 1000 V

Included:

- Red and black alligator clips with nickel-plated jaws

AC385-RGB

AC385-RGB SureGrip™ Alligator Clip Set, CAT III 1500 V / CAT IV 1000 V

Included:

- Red, black, and green alligator clips with nickel-plated jaws
-

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2025 Fluke Corporation.
Specifications subject to change without notice.
12/2025

**Modification of this document is not permitted
without written permission from Fluke
Corporation.**