



Green Cell Uninterruptible Power Supply UPS 800VA 500W with LCD Display PowerCore 12 VDC

Code:

UPSLPPC500

EAN:

5904326376601

Product code :	UPSLPPC500
Model :	UPSLPPC500
Voltage	12V
Overheating protection :	Yes
Deep discharge protection	Yes
Indicator :	LCD
Input frequency	45-65 Hz
Output voltage shape :	Pure Sine
Sockets	2x Schuko
Maximum current :	13A
Usable power (continuous)	500W
Topology :	Line-Interactive AVR
Noise level :	≤55dB
Dimensions :	160x240x390mm
Guarantee :	24 months
Switching time :	2-6 ms

Producer :	Greencell
Apparent power :	800VA
Security :	reverse battery connection
Overcharge protection :	Yes
Short circuit protection :	Yes
Input voltage :	155-285V~
Output voltage :	230V
Additional features :	Physical mute switch
Operating temperature :	from -5° C to 40° C
Storage temperature :	from -15° V to 45° C
Standard charging current :	3 levels for user selection: Low(3A~6A), Medium:(7A~9A), High:(11A~14A)
Degree of protection :	IP20
Possibility of connecting an external battery :	Yes
Condition :	Brand new
Battery compatibility :	12VDC