



Green Cell Uninterruptible Power Supply UPS 1200VA 800W with LCD Display

Code: **UPSLPPC800**
EAN: **5904326376618**

Voltage	12V
Warranty	6 months
Overheat protection	Yes
Overdischarge protection	Yes
Overcharge protection	Yes
Product code	UPSLPPC800
Size	160x240x390mm
Input Voltage	155-285V~
Input frequency	45-65Hz
Sockets	2x Schuko
Indicator	LCD
Model	UPSLPPC800
Working temperature	od -5° C do 40° C
Additional features:	Fizyczny przełącznik wyciszenia
Shape of the output voltage	Pure Sinusoid
Storage temperature	od -15° C do 45° C
Maximum current	18A
Usable power (continuous)	800W
Apparent power	1200VA
Topology	Line-Interactive AVR
Loudness	≤55dB
Short circuit protection	Yes

Safety	odwrotne podłączenie akumulatora
Stopień ochrony	IP20
Standardowy prąd ładowania	3 poziomy do wyboru przez użytkownika: Niski: (4A~7A), Średni: (8A~11A), Wysoki: (15A~19A)
Wilgotność środowiska pracy	10-90%, bez kondensacji
Kompatybilność baterii	12 VDC
Czas przełączenia	2-6 ms
Typ baterii	Akumulator kwasowo-ołowiowy