



Green Cell Uninterruptible Power Supply UPS 2000VA 1200W with LCD Display

Code: **UPSLPPC1200**
EAN: **5904326376632**

Warranty	24 months
Overheat protection	Yes
Overdischarge protection	Yes
Overcharge protection	Yes
Product code	UPSLPPC1200
Size	160x240x390mm
Input Voltage	155-285V~
Input frequency	45-65Hz
Sockets	2x Schuko
Indicator	LCD
Model	UPSLPPC1200
Working temperature	od -5°C do 40°C
Additional features:	Fizyczny przełącznik wyciszenia
Shape of the output voltage	Pure Sinusoid
Storage temperature	Temperatura przechowywania
Maximum current	13 A
Usable power (continuous)	1200W
Apparent power	2000VA
Topology	Line-Interactive AVR
Loudness	≤55dB
Short circuit protection	Yes
Safety	odwrotne podłączenie akumulatora

Stopień ochrony	IP20
Standardowy prąd ładowania	3 poziomy do wyboru przez użytkownika: Niski(3A~6A), Średni:(7A~9A), Wysoki:(11A~4A)
Wilgotność środowiska pracy	10-90%, bez kondensacji
Kompatybilność baterii	24 VDC
Czas przełączenia	2-6 ms
Typ baterii	Akumulator kwasowo-ołowiowy