

12V | 1000A

GB40



START DEAD BATTERIES. ULTRASAFE® LITHIUM JUMP STARTER.™

GAS & DIESEL

UP TO 6.0L GAS & 3.0L DIESEL.

Designed for gas engines up to 6 Liters and diesel engines up to 3 Liters for cars, boats, lawn mowers and more.

USB

CHARGE & RECHARGE.

It's internal battery can be used to recharge any personal mobile devices like smartphones, tablets, or any other USB device, and can be recharged by any powered USB port.

20X

UP TO 20 JUMPSTARTS.

Compact, yet powerful lithium jump starter rated at 1,000 Amps. Full power to jump start a vehicle up to 20 times on a single charge.

ULTRA SAFE

SPARK PROOF TECHNOLOGY.

Safely connect to any 12-volt car battery with our mistake-proof design featuring spark-proof technology and reverse polarity protection.



NOCO

30339 Diamond Parkway, #102
Glenwillow, OH 44139 | USA
1.800.456.6626

no.co

LEAD ACID

WET

GEL

MF

EFB

AGM

AUTO | MARINE | RV | POWERSPORT | LAWN & GARDEN



INTERFACE

POWER LED

The jump starter is in standby or the battery voltage is too low for the jump starter to detect.



POWER BUTTON

Push to turn unit "On" & "Off".



CHARGE LED

Indicates the charge level of the internal battery.



BOOST LED

Illuminates white when boost is active. The LED flashes white when manual override feature is active.



LIGHT MODE BUTTON

Toggles the ultra-bright LED light through 7 light modes: 100% > 50% > 10% > SOS > Blink > Strobe > Off



ERROR

Blinks "on" and "off" when the internal battery is too hot/too cold.




MANUAL OVERRIDE.


Press and hold the manual override button for 3 seconds, until the Boost LED starts flashing, to enter into manual mode.



WHAT'S IN THE BOX



*Accessories not to scale with GB40



CHARGE DEVICES.

Recharge your personal devices on the go, like smartphones, tablets, e-watches and more - up to 4 smartphone recharges.

RECHARGE TIME

0.5A	12hr
1A	6hr
2A	3hr

TECHNICAL SPECIFICATIONS

INTERNAL BATTERY:	24 Watt-Hour Lithium Ion
PEAK CURRENT RATING:	1000A
OPERATING TEMPERATURE:	-4°F to +122°F (-20°C to +50°C)
CHARGING TEMPERATURE:	32°F to +104°F (0°C to +40°C)
USB (INPUT):	5V, 2.1A
USB (OUTPUT):	5V, 2.1A
HOUSING PROTECTION:	IP65 (w/Ports Closed)
COOLING:	Natural Convection
UNIT WEIGHT:	1.65 lbs (0.74kg)
UNIT WEIGHT W/ CLAMPS & ACCESSORIES:	2.4 lbs (1.08kg)
LED FLASHLIGHT:	100 Lumens
VOLUMETRICS:	Retail Packaging: Dimensions: 3.62"x4.57"x8.27" Weight: 2.75lbs UPC: 0-46221-15002-5 Master Carton: Dimensions: 9.25"x12.60"x11.22" Weight: 18.30lbs Quantity: 6 UPC: 10046221150022 Inner Carton: Dimensions: 4.01"x8.78"x5.12" Weight: 2.89lbs Units Per Pallet: NA - 360 Units EU - 270 Units

NOCO

30339 Diamond Parkway, #102
Glenwillow, OH 44139 | USA
1.800.456.6626

no.co

