

DATASHEET


Rocker On/Off Switch, Connection Type-C 7/16 plug with Waterproof box, IP67














BN	Applicable cable diameter	Casing button Colour	Colours (LEDs)
3747156	5 - 8 mm	Black and Orange	Orange
3747158	5 - 8 mm	Black and Red	Red
3747159	5 - 8 mm	Black and Green	Green
3747160	7 - 10 mm	Black and Orange	Orange
3747161	7 - 10 mm	Black and Red	Red
3747163	7 - 10 mm	Black and Green	Green

All dimensions in mm

Technical data

Waterproof box colour ..... Black
Functions ..... Latch
Bulb type ..... LED
Connection ..... Type-C CEE 7/16 plug 6.3 mm
Nominal voltage ..... 250 V/AC
Nominal current ..... 16 A
Front panel thickness ..... 2 mm
Front panel cut-out ..... 22 x 30.2 mm
IP rating IP67
On/Off switch 2

Mechanical life ..... 300,000 switching cycles
Tempureature range ..... -10 to +80 °C
Print motif 0/I
Material ..... Thermoplastic
Contact material ..... Cu-alloy, nickel plated
Contact resistance ..... ≤100 mΩ
Insulation resistance ..... ≥100 MΩ
Number of pins 4
Dielectric strength ..... ≥1500 V AC / 5 mA / 5 s
Dimensions (L x W x H) ..... 116 x 57 x 55 mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.