

VARTA Outdoor Sports Lantern L10 4AA w/o Batt.



Light up every adventure: Robust outdoor lantern with weather-resistant and shockproof design, 2 light modes and built-in hook for flexible mounting.



Information

- Robust and compact outdoor lantern
- Perfect for camping, hiking, road trips, family adventures, or as emergency home light
- 2 light modes: high and low
- High performance LED
- 360° light distribution to illuminate the surrounding
- Rubber elements for grip and protection in outdoor environments
- Water- and dust resistant (IP54) and shock proof (1m drop test)
- Integrated hook for easy and flexible mounting
- Battery driven (4x AA, not incl.)

Article Details

Ordernumber	16550 101 111
RCP (incl. Tax)	17.99 EUR
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	10.00 m
Runtime	70 h
Total light output	170 lm
Product Diameter mm	91.00
Product Weight g	262.00

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 225446	103.00	100.00	200.00	0.36
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	4	40 08496 225453	220.00	220.00	220.00	1.59
PAL (Pallet)	240	40 08496 225491	800.00	1,200.00	1,030.00	116.70
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
4	15		60		0	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.
VARTA Consumer Batteries GmbH & Co. KGaA | Sales Germany | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 770 | Fax (+49) 827 827 4

