
DATASHEET

CAM switch

EPO Rotatory switches

Item no 3758675






Operation type	EPO rotary switch
Switching voltage	690 V/AC (at 50 Hz)
Switching current (max.)	20 A
Poles	2-pole
Switching angle	1 x 90 °
Functions (switches)	Latch
Imprint	OFF/ON
Color	Yellow/Red
Connection	Screws
Operating temperature	-5 °C to +40 °C

Item no 3758672






Operation type ..... EPO rotary switch
Switching voltage ..... 690 V/AC (at 50 Hz)
Switching current (max.) ..... 20 A
Poles 4-pole
Switching angle ..... 1 x 90°
Functions (switches) ..... Latch
Imprint ..... OFF/ON
Color ..... Yellow/Red
Connection ..... Screws
Operating temperature ..... -5 °C to +40 °C


Item no 3758674






Operation type ..... EPO rotary switch
Switching voltage ..... 690 V/AC (at 50 Hz)
Switching current (max.) ..... 20 A
Poles 4-pole
Switching angle ..... 1 x 90 °
Functions (switches) ..... Latch
Imprint ..... OFF/ON
Color ..... Yellow/Red
Connection ..... Screws
Operating temperature ..... -5 °C to +40 °C

Item no 3758744






Operation type	EPO rotary switch
Switching voltage	690 V/AC (at 50 Hz)
Switching current (max.)	20 A
Poles	3-pole+N
Switching angle	1 x 90 °
Functions (switches)	Latch
Imprint	3758675 OFF/ON
Color	Yellow/Red
Connection	Screws
Operating temperature	-5 °C
Max. temperature	40 °C
Type (misc.)	Surface-mounted main switch
Operating temperature	-5 °C to +40 °C

Toggle switches

Item no 3758746






Operation type ..... Toggle
Switching voltage ..... 690 V/AC (at 50 Hz)
Switching current (max.) ..... 20 A
Poles 4-pole
Switching angle ..... 1 x 45 °
Functions (switches) ..... Latch
Imprint 0/1
Color ..... Black/Grey
Mounting type ..... Recess-mount
Connection ..... Screws
Operating temperature ..... -5 °C to +40 °C

Item no 3758673






Operation type ..... Toggle
Switching voltage ..... 690 V/AC (at 50 Hz)
Switching current (max.) ..... 20 A
Poles 4-pole
Switching angle ..... 1 x 60 °
Functions (switches) ..... Latch
Imprint 0/1
Color ..... Black/Grey
Connection ..... Screws
Recess diameter ..... 22.3 mm
perating temperature ..... -5 °C to +40 °C

Item no 3758676






Operation type	Toggle
Switching voltage	690 V/AC (at 50 Hz)
Switching current (max.)	20 A
Poles	2-pole
Switching angle	2 x 45 °
Functions (switches)	Latch
Imprint	1/0/2
Color	Black/Grey
Mounting type	Recess-mount
Connection	Screws
Operating temperature	-5 °C to +40 °C

Item no 3758745





Switching voltage	690 V/AC (at 50 Hz)
Switching current (max.)	20 A
Poles	2-pole
Switching angle	1 x 90 °
Functions (switches)	Latch
Imprint	OFF/ON
Color	Black/Grey
Mounting type	Recess-mount
Connection	Screws
Operating temperature	-5 °C to +40 °C

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.