

Keppower Protected 18500 3.7V 2300 mAh (P1850C3)

No.	Item	Details	Remarks
1.1	Product Name	Keppower Protected 18500 3.7V 2300mAh (P1850C3)	
1.2	Supplier	Keppower Technology Co., Limited	
1.3	Cell	CHINA 18500 2300mAH	
1.4	Capacity	Min. 2200 mAh; Normal: 2300mAh	Discharge:0.2CmA
1.5	Normal Volatge	3.70V	
1.6	Stanard Charge voltage	4.20V	
1.7	Standard Charge current	1150mA	
1.8	Charge Time(Std.)	5 hours	
1.9	Standard Discharge Cut-off Voltage	2.5V	
1.10	Standard Discharge current	460mA	
1.11	Standard Discharge cut off current	30mA	
1.12	PCB Protection trip current	Above 7A	
1.13	Max. continuous discharge current	4.6A	
1.14	Storage Temperature	-20°C ~ +60°C	Less than 1 month
1.15		-20°C ~ +45°C	Less than 3 months
1.16	Weight	Max 37.5g	
1.17	Size	(L)52.80mm*(D)18.75mm	

www.keppower.com.cn