

EU Declaration of Conformity

Model name:	SNP30-12/24VF-3, SS30-12/24VF, SNP40-12/24VF,F15-350,15-12D,36-12D SNP50-12/24VF-1, SE15-12/24VFP, SNP75-12/24VFP,SE20-5/12/24VFP, SS30-12/24VFP,SS40-12/24VFP,SS60-12/24VFP,SNP100-12/24VFP,SNP60-12/24VFP-1,SNP100-12/24VFP-1,SNP150-12/24VFP-1,SIM-IR,SIK-IR, SIL-PIR,SNP40-12/24VF(UE),SNP60-12/24VF(UE),SNP30-12VFC,SNP30-24VFC, SNP60-12VFC,SNP60-24VFC,SNP100-12VFC,SNP100-24VFC, SS20-12/24VF, SS60-12/24VF,SSL60-12/24/48VF,SL75-12/24VF,SE30-12/24VL,SS30-12/24VL,SE60-12/24VL,SS60-12/24VL, SEA60-12/24VL, SEA75-12/24VL,SS75-12/24VL, SS24-12/24VL, SS30-12/24vL,SE8-12/24VL, SEA8-12/24VL, SE15-12/24VF,SE20-12/24VF,SEA15-12/24VL, SNP30-12/24VF-2,SNP45-12/24VF-1,SL100-12/24/48VF-1,SL150-12/24/48VF-1,SNP24-12/24VLW SL60-12VF-1,SL60-24VF-1,SL60-48VF-1,SL75-12/24VF,SL100-24VF, SNP100-12VF, SNP100-24VF, SNP150-12/24VF,SL30-12VF,SL30-24VF,SL75-12/24VFT, SL100-12/24VFT,SL150-12/24VFT SE100-12/24VL, SE150-12/24VL,SNP150-12VF-1,SNP150-24VF-1,SNP200-24VF-1 SNP200-12VF-1, SL200-24VF,SL240-24VF,SL100-48VF,SL200-48VF, SS30-12/24VF,SS50-12/24VF,SS50-12/24VL,SNP100-12VL(UE), SS100-12/24VL,SNP150-12/24VL,SS150-12/24VL,SP30-12VFT,SP30-24VFT,SP30-12VFT-1,SP30-24VFT-1,SP50-12VFT,SP50-24VFT,SP50-12VFT-1,SP50-24VFT-1,SP75-12VLT, SP75-24VLT, SP100-12VLT,SP100-24VLT,SP150-12VLT,SP150-24VLT,SCL100-12/24/48VF, SCL150-12/24/48VF SL100-12VL(UE),SL100-24VF(UE),SL150-12VF(UE),SL15 -24VF(UE) SDL60-48VF6, SDL100-48VF6, SDL150-48VF6, SDN200-48VL6, SDS8-700IL, SDS15-350IL,SDS15-700IL, SDS26-700IL,SDS44-1050IL,SDS60-1400IL, SPA250-12/24VFP, SPA320-12/24VFP,SE15-350/500/700IF SNP200-12/24/48VL, SNP200-12/24/48VL-1,SNP250-12/24/48VL,SNP250-12/24/48VL-1,SNP320-12/24/48VL,SNP320-12/24/48VL-1 SPF24-12/24VSP,SPF35-12/24VSP,SPF60-12/24VSP,SPF100-12/24VSP, SPF150-12/24VSP SPE100-12/24VLP, SPE200-12/24VLP,SPE320-12/24VLP,SPG50-12/24V,SPG80-12/24V,SPG100-12/24/48V,SPG150-12/24/48V,SPG200-12/24/48V,SPG240-12/24/48V,SPG320-12/24/48V,SPG350-12/24V
Name and address of the manufacturer:	NINGBO SNAPPY OPTOELECTRONICS CO., LTD ADD:No.1228 Jianlan Road, National Hi-tech Park of Ningbo,315040, Zhejiang, P.R. China
The object of the declaration described above is in conformity with the relevant Union harmonisation legislation:	2014/30/EU (EMC) 2014/35/EU (LVD) 2011/65/EU(RoHS) (EU) 2015/863 Energy-Related Product Directive (2009/125/EC) implementing measure COMMISSION REGULATION (UE) n. 2019/2020



Ningbo Snappy Optoelectronics Co.,Ltd. No.1228 Jianlan Road, National Hi-tech Park of Ningbo,315040, Zhejiang, P.R. China

References to the relevant harmonised standards used:	EN61347-1:2015 EN61347-2-13:2014+A1 EN55015:2019+A11 EN61547:2009 EN61000-3-2:2019 EN61000-3-3:2013
Signed for and on behalf of:	NINGBO SNAPPY OPTOELECTRONICS CO., LTD
Place and date of issue:	NINGBO,CHINA 2026-01-05
Name, Function, Signature:	Marketing Director: Victoria Zhao

This declaration of conformity is issued under the sole responsibility of the manufacturer.

宁波赛耐比光电科技有限公司
NINGBO SNAPPY OPTOELECTRONICS CO., LTD.
张莉