
SMBM-BNCM174XX

(Cable Assembly Coaxial SMB Male to BNC Male RG-174)





Mueller Electric Company
2850 Gilchrist Rd. Bld 5A
Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629
Phone: 330.780.2525
Fax: 330.780.2524

Electrical Ratings

Electrical ratings of a cable assembly are determined by the limiting connector type and cable size.

Connector	Cable	Connector Impedance (Ohms)	Frequency (GHz)	VSWR
SMB	RG-174	50	0-3	1.35 MAX
BNC	RG-174	50	0-3	1.35 MAX

Product Attributes

Gender	Male to Male
Style	SMB to BNC
1st Connector	Gold Plated SMB Male Plug w/ PTFE Insulator
2nd Connector	Gold Plated BNC Male Plug w/ PTFE Insulator
Features	Shielded
Operating Temperature	-30°C (-22°F) to 70°C (158°F)
SMBM-BNCM17405 SMBM-BNCM17410	0.5M 1M
RoHS 3 Compliant	

Mueller Electric Company
2850 Gilchrist Rd. Bld 5A
Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629
Phone: 330.780.2525
Fax: 330.780.2524