



Meaningful Innovation.

WEEE Number: 80133970

INSTRUCTION MANUAL

LED BACKLIT SURFACE MOUNTED PANEL



TECHNICAL DATA

MODEL	SKU	SHAPE	WATTS	LUMENS	BEAM ANGLE	IP RATING	CRI	BODY TYPE	TOTAL CURRENT	INPUT VOLTAGE	LIFE SPAN [HOURS]	ON/OFF CYCLE [TIMES]	DIMENSION (LxWxH)
VT-60006CCT	78706	ROUND	6W	630 Lm	120°	IP20	>80	PLASTIC	36mA	AC:220-240 50/60Hz	30,000	>15000	121.2x30.6mm
VT-60012CCT	78736		12W	1320 Lm	120°	IP20	>80	PLASTIC	71mA	AC:220-240 50/60Hz	30,000	>15000	167.4x30.7mm
VT-60018CCT	78766		18W	1980 Lm	120°	IP20	>80	PLASTIC	103mA	AC:220-240 50/60Hz	30,000	>15000	215.6x30.8mm
VT-60024CCT	78796		24W	2640 Lm	120°	IP20	>80	PLASTIC	160mA	AC:220-240 50/60Hz	30,000	>15000	288.6x31.2mm
VT-60006CCT	104926	SQUARE	6W	630 Lm	120°	IP20	>80	PLASTIC	36mA	AC:220-240 50/60Hz	30,000	>15000	120.8x120.8x30.7mm
VT-60012CCT	104956		12W	1320 Lm	120°	IP20	>80	PLASTIC	71mA	AC:220-240 50/60Hz	30,000	>15000	167.3x167.3x30.7mm
VT-60018CCT	104986		18W	1980 Lm	120°	IP20	>80	PLASTIC	103mA	AC:220-240 50/60Hz	30,000	>15000	214x214x31mm
VT-60024CCT	105146		24W	2640 Lm	120°	IP20	>80	PLASTIC	160mA	AC:220-240 50/60Hz	30,000	>15000	287x287x30.7mm

This product contains a light source of energy efficiency class <F/E>', where <F/E> shall be replaced by the energy efficiency class of the contained light source.

INTRODUCTION & WARRANTY

Thank you for selecting and buying V-TAC product. V-TAC will serve you the best. Please read these instructions carefully before starting the installation and keep this manual handy for future reference. If you have any another query, please contact our dealer or local vendor from whom you have purchased the product. They are trained and ready to serve you at the best. The warranty is valid for 6 years from the date of purchase. The warranty does not apply to damage caused by incorrect installation or abnormal wear and tear. The company gives no warranty against damage to any surface due to incorrect removal and installation of the product. The products are suitable for 10-12 Hours Daily operation. Usage of product for 24 Hours a day would void the warranty. This product is warranted for manufacturing defects only.

WARNING

- Please make sure to turn off the power before starting the installation.
- Installation must be performed by a certified person.
- If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.
- Method of attachment of the cable or cord such that any replacement can only be made by the manufacturer, his service agent or similar qualified person.
- For Indoor use only.



**6 YEAR
WARRANTY***




**MULTI-LANGUAGE
MANUAL QR CODE**

Please scan the QR code
to access the manual in
multiple languages.



IN CASE OF ANY QUERY/ISSUE WITH THE PRODUCT, PLEASE REACH OUT TO US AT: SUPPORT@V-TAC.EU
FOR MORE PRODUCTS RANGE, INQUIRY PLEASE CONTACT OUR DISTRIBUTOR OR NEAREST DEALERS. V-TAC
EUROPE LTD. BULGARIA, PLOVDIV 4000, BUL.L.KARAVELOW 9B



This marking indicates that this product should not be disposed of with other household wastes.



Caution, risk of electric shock.



Points de collecte sur www.quefairedemesdechets.fr
Privilégiez la réparation ou le don de votre appareil !

ATTENTION!

Do not look directly at the LED light beam. Use the product only with the rated voltage or within the specified range. Do not operate the product if the protective cover is damaged. Avoid using it in adverse conditions such as dust, water, moisture, vibrations, explosive atmospheres, or chemical fumes. Strong electromagnetic interference may disrupt product performance.


USAGE GUIDELINES/MAINTENANCE

Perform all maintenance only after disconnecting the power supply and allowing the product to cool. Clean with a soft, dry cloth only; do not use chemical cleaners. Do not cover the product and ensure adequate airflow, as it may reach high temperatures during operation.

MOUNTING

Read the manual before installation. Installation must be carried out by a qualified electrician. Exercise caution: the product includes a protective contact/terminal, and failure to connect it may result in electric shock. Refer to the mounting diagram for guidance. Ensure proper mechanical fastening and electrical connection before first use.

WIRING DIAGRAM









INSTALLATION DIAGRAM

1. Switch OFF the power before beginning installation.	2. Confirm the bracket installation position.	3. Drill the mounting hole.
4. Insert the expansion bolt.	5. Secure the included bracket to the ceiling with screws.	6. Connect the wiring according to the wiring diagram. 7. Adjust the color temperature using the CCT switch.
8. Install the panel into the bracket.	9. Fasten the light with screws.	10. Turn on the power and test the light.

DISASSEMBLY DIAGRAM

(For Market surveillance team only)

 1.Power off the unit, tap the center of the diffusion plate with a pointed tool, and remove the damaged plate.	 2. Disconnect the power wire from the plug terminal.	 3. If there is no hot-melt column or it is not fused, skip this step. If the hot-melt column is fused to secure the aluminum substrate, cut the fused section with diagonal pliers.
 4. Push the buckle outward to release and remove the aluminum substrate pressing strip from the bayonet. This step is required only for the 24W panel light.	 5. Push the buckle outward to release the aluminum substrate, then remove the light source board.	 6. Insert a two-core cable (18—22 AWG) into the plug-in terminal, then connect the external power supply for testing.

Note: Light source removal will void the warranty

V-TAC WEST EUROPE LTD. IN CASE OF ANY QUERY/ISSUE WITH THE PRODUCT, PLEASE REACH OUT TO US AT: SUPPORT@V-TAC.EU FOR MORE PRODUCTS RANGE, INQUIRY PLEASE CONTACT OUR DISTRIBUTOR OR NEAREST DEALERS. V-TAC WEST EUROPE LTD. GROUND FLOOR, 71 LOWER BAGGOT STREET, DUBLIN 02, IRELAND DO2 P593

V-TAC UK LTD. IN CASE OF ANY QUERY/ISSUE WITH THE PRODUCT PLEASE REACH OUT TO US AT SUPPORT@VTACEXPORTS.COM V-TAC, 5A TUNGSTEN PARK, DOWNS ROAD, WITNEY, OXFORDSHIRE, OX29 0AX

