



Meaningful Innovation.

INSTRUCTION MANUAL LED FLOOD LIGHT



**IP65
RATING**


TECHNICAL DATA

MODEL	SKU	WATTS	USEFUL LUMENS @WIDE CONE	BEAM ANGLE	LIFE SPAN [HOURS]	DF	CRI	INPUT VOLTAGE	OPERATION TEMPERATURE	DIMENSION	BODY TYPE	N.W [KGS]	MAX MOUNTING HEIGHT	PROJECTED AREA [MMP]	IK RATING
VT-44033	231976 231986	30W	3450 lm	115°	30,000	>0.9	>70	AC: 220-240V 50Hz	-20° to +45°C	164x34x144mm	Aluminium	0.41	<5M	23616	IK05
VT-4455	231996 232166 232176	50W	5740 lm	115°	30,000	>0.9	>70	AC: 220-240V 50Hz	-20° to +45°C	185x162x35mm	Aluminium	0.56	<5M	29970	IK05
VT-44101	232006 232186 232196	100W	11480 lm	115°	30,000	>0.9	>70	AC: 220-240V 50Hz	-20° to +45°C	256x229x42mm	Aluminium	1.1	<5M	58624	IK05
VT-44153	232016 232026	150W	17220 lm	115°	30,000	>0.9	>70	AC: 220-240V 50Hz	-20° to +45°C	331x47x278mm	Aluminium	1.78	<5M	92018	IK05
VT-44201	232206 232216	200W	22960 lm	115°	30,000	>0.9	>70	AC: 220-240V 50Hz	-20° to +45°C	406x333x47mm	Aluminium	2.8	<5M	135198	IK05
VT-44003	232036 238256	300W	34440 lm	115°	30,000	>0.9	>70	AC: 220-240V 50Hz	-20° to +45°C	498x411.6x48mm	Aluminium	4.39	<5M	204977	IK05

*This product contains a light source of energy efficiency class<D>, where <D> shall be replaced by the energy efficiency class of the contained light source.

INTRODUCTION & WARRANTY

Thank you for selecting and buying V-TAC product. V-TAC will serve you the best. Please read these instructions carefully before starting the installing and keep this manual handy for future reference. If you have any another query, please contact our dealer or local vendor from whom you have purchased the product. They are trained and ready to serve you at the best. The warranty is valid for 6 years from the date of purchase. The warranty does not apply to damage caused by incorrect installation or abnormal wear and tear. The company gives no warranty against damage to any surface due to incorrect removal and installation of the product. The products are suitable for 10-12 Hours Daily operation. Usage of product for 24 Hours a day would void the warranty. This product is warranted for manufacturing defects only.



MULTI-LANGUAGE MANUAL QR CODE

Please scan the QR code to access the manual in multiple languages.



FR

Cet appareil,
ses accessoires
et cordons
se recyclent

À DÉPOSER
EN MAGASIN



ou

À DÉPOSER
EN DÉCHÈTERIE



Points de collecte sur www.quefairedemesdechets.fr
Privilégiez la réparation ou le don de votre appareil !


IN CASE OF ANY QUERY/ISSUE WITH THE PRODUCT, PLEASE REACH OUT TO US AT:
SUPPORT@V-TAC.EU FOR MORE PRODUCTS RANGE, INQUIRY PLEASE CONTACT OUR DISTRIBUTOR
OR NEAREST DEALERS. V-TAC EUROPE LTD. BULGARIA, PLOVDIV 4000, BUL.L.KARAVELOW 9B

WARNING

- Please make sure to turn off the power before starting the installation.
- Installation must be performed by a qualified electrician.
- The light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced.
- The control gear of this luminaire is a non-replaceable component; when the control gear reaches its end of life the whole luminaire shall be replaced.
- The external flexible cable or cord of this luminaire cannot be replaced; if the cord is damaged, the luminaire shall be destroyed.
- Terminal block not included. Must be connected to waterproof terminal box.
- Proper grounding should be ensured throughout the installation.
- For outdoor use.
- Replace any cracked protective shield.  → 
- Minimum distance from lighted objects 1m. 

NOTE

- To reduce the risk of strangulation the flexible wiring connected to this luminaire shall be effectively fixed to the wall. Only to be installed outside arm's reach.
- In order to maintain the IP protection of the product, the cable entry/gland should be installed on the bottom side.



Caution, risk of electric shock.



This marking indicates that this product should not be disposed of with other household wastes.

INSTALLATION DIAGRAM

1

2

3

4

5

WIRE LENGTH	
30W	15cm
50W	15cm
100W	100cm
150W	100cm
200W	100cm
300W	100cm

Blue   N 

Y./Grn.   

Brown   L 

INSTALLATION INSTRUCTION

- DO NOT USE IN AREAS WITH LIMITED VENTILATION OR OUTSIDE THE RATED AMBIENT TEMPERATURE RANGE. *CONNECT WITH WATERPROOF CABLE HOUSE ONLY. *ENSURE ELECTRICITY IS SWITCH OFF BEFORE INSTALLATION.


- Please do not mount to a surface that is prone to vibrations.*

Remove the screw and the bracket afterward. (Figure 1) Before drilling, mark the hole position for fixing the bracket onto the wall (Screw not supplied). (Figure 2)

- Screw the retaining bracket to the wall with a suitable quantity of screws. (Figure 4)
- Mount the bracket back to the fixture. Adjust the floodlight according to the desired position. Tighten the screw. (Figure 5) Connect your main cable (HO5RN-F3G1.0mm2 Recommended) with the input lead of our product through the waterproof junction box. Note, the line (-) of the lead. (Need to use the junction box of IP65 or above, ensure to tighten the waterproof screw) Switch on the power to make sure if the product is working.


DISMANTLING INSTRUCTIONS

(For Market surveillance team only)



Note

- Light source removal will void the warranty.
- The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.



V-TAC WEST EUROPE LTD. IN CASE OF ANY QUERY/ISSUE WITH THE PRODUCT, PLEASE REACH OUT TO US AT: SUPPORT@V-TAC.EU FOR MORE PRODUCTS RANGE, INQUIRY PLEASE CONTACT OUR DISTRIBUTOR OR NEAREST DEALERS. V-TAC WEST EUROPE LTD. GROUND FLOOR, 71 LOWER BAGGOT STREET, DUBLIN O2, IRELAND DO2 P593

V-TAC UK LTD. IN CASE OF ANY QUERY/ISSUE WITH THE PRODUCT PLEASE REACH OUT TO US AT SUPPORT@VTACEXPORTS.COM V-TAC, 5A TUNGSTEN PARK, DOWNS ROAD, WITNEY, OXFORDSHIRE, OX29 OAX

