LogiLink®
PROFESSIONAL



Cat.6A S/FTP Patch Cable SlimLine

Technical Features

Cat.6A 500 MHz RJ45 patch cable


Foil shielded and pairs in metal foil (PIMF)

Low smoke zero halogen (LSZH)

4 x 2 x 28/7 AWG bare copper cable

Suitable for PoE (IEEE 802.3af) & PoE+ (IEEE 802.3at)

Technical Drawings



Unit: mm

www.2direct.de

Made in China

* The specifications and pictures are subject to change without notice.
* All trade names referenced are the registered trademarks of their respective owners.

Length	White	EAN Code
0.15 m	CP5001S	4052792084153
0.25 m	CP5011S	4052792083095
0.50 m	CP5021S	4052792083101
1.00 m	CP5031S	4052792083118
1.50 m	CP5041S	4052792083125
2.00 m	CP5051S	4052792083132
3.00 m	CP5061S	4052792083149
5.00 m	CP5071S	4052792083156
7.50 m	CP5081S	4052792083163
10.00 m	CP5091S	4052792083170
15.00 m	CP5101S	4052792083187
20.00 m	CP5111S	4052792083194



Length	Grey	EAN Code	Black	EAN Code
0.15 m	CP5002S	4052792084139	CP5003S	4052792084108
0.25 m	CP5012S	4052792082876	CP5013S	4052792082548
0.50 m	CP5022S	4052792082883	CP5023S	4052792082555
1.00 m	CP5032S	4052792082890	CP5033S	4052792082562
1.50 m	CP5042S	4052792082906	CP5043S	4052792082579
2.00 m	CP5052S	4052792082913	CP5053S	4052792082586
3.00 m	CP5062S	4052792082920	CP5063S	4052792082593
5.00 m	CP5072S	4052792082937	CP5073S	4052792082609
7.50 m	CP5082S	4052792082944	CP5083S	4052792082616
10.00 m	CP5092S	4052792082951	CP5093S	4052792082623
15.00 m	CP5102S	4052792082968	CP5103S	4052792082630
20.00 m	CP5112S	4052792082975	CP5113S	4052792082647

www.2direct.de

Made in China

* The specifications and pictures are subject to change without notice.
* All trade names referenced are the registered trademarks of their respective owners.

LogiLink®
PROFESSIONAL

Length	Red	EAN Code	Green	EAN Code
0.15 m	CP5004S	4052792084146	CP5005S	4052792084122
0.25 m	CP5014S	4052792082982	CP5015S	4052792082760
0.50 m	CP5024S	4052792082999	CP5025S	4052792082777
1.00 m	CP5034S	4052792083002	CP5035S	4052792082784
1.50 m	CP5044S	4052792083019	CP5045S	4052792082791
2.00 m	CP5054S	4052792083026	CP5055S	4052792082807
3.00 m	CP5064S	4052792083033	CP5065S	4052792082814
5.00 m	CP5074S	4052792083040	CP5075S	4052792082821
7.50 m	CP5084S	4052792083057	CP5085S	4052792082838
10.00 m	CP5094S	4052792083064	CP5095S	4052792082845
15.00 m	CP5104S	4052792083071	CP5105S	4052792082852
20.00 m	CP5114S	4052792083088	CP5115S	4052792082869

Length	Blue	EAN Code	Yellow	EAN Code
0.15 m	CP5006S	4052792084115	CP5007S	4052792084160
0.25 m	CP5016S	4052792082654	CP5017S	4052792083200
0.50 m	CP5026S	4052792082661	CP5027S	4052792083217
1.00 m	CP5036S	4052792082678	CP5037S	4052792083224
1.50 m	CP5046S	4052792082685	CP5047S	4052792083231
2.00 m	CP5056S	4052792082692	CP5057S	4052792083248
3.00 m	CP5066S	4052792082708	CP5067S	4052792083262
5.00 m	CP5076S	4052792082715	CP5077S	4052792083279
7.50 m	CP5086S	4052792082722	CP5087S	4052792083286
10.00 m	CP5096S	4052792082739	CP5097S	4052792083293
15.00 m	CP5106S	4052792082746	CP5107S	4052792083309
20.00 m	CP5116S	4052792082753	CP5117S	4052792083316

www.2direct.de

Made in China

* The specifications and pictures are subject to change without notice.
* All trade names referenced are the registered trademarks of their respective owners.

Package Content

1x Cat.6A S/FTP Patch Cable

Packaging Information

Cable Length	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
0.15 m	60 x 350 mm	0.011 kg	400 x 300 x 250 mm	650 pcs	7.5 kg
0.25 m	60 x 350 mm	0.013 kg	400 x 300 x 250 mm	500 pcs	7.2 kg
0.50 m	160 x 190 mm	0.018 kg	400 x 300 x 300 mm	400 pcs	7.9 kg
1.00 m	160 x 190 mm	0.029 kg	400 x 300 x 300 mm	250 pcs	7.8 kg
1.50 m	160 x 190 mm	0.039 kg	400 x 300 x 250 mm	200 pcs	8.3 kg
2.00 m	160 x 190 mm	0.047 kg	400 x 300 x 300 mm	200 pcs	9.8 kg
3.00 m	160 x 190 mm	0.069 kg	400 x 300 x 320 mm	150 pcs	10.9 kg
5.00 m	160 x 190 mm	0.108 kg	400 x 300 x 300 mm	100 pcs	11.4 kg
7.50 m	160 x 190 mm	0.143 kg	400 x 300 x 250 mm	60 pcs	9.1 kg
10.00 m	200 x 230 mm	0.190 kg	400 x 300 x 300 mm	50 pcs	10.1 kg
15.00 m	200 x 230 mm	0.302 kg	400 x 300 x 300 mm	40 pcs	12.7 kg
20.00 m	200 x 230 mm	0.380 kg	400 x 300 x 250 mm	20 pcs	8.1 kg

Made in China

* The specifications and pictures are subject to change without notice.
* All trade names referenced are the registered trademarks of their respective owners.