ESD Tape Dispenser with ESD Grid Tapes
Part-No. 26EC177



Specification:

Material: ABS
Color: Black
Product Dimension: L: 105 x W: 57 x H: 49 mm (unit: mm +/- 0.5)
Suitable Tape dimensionl: Ø 62mm x W: 22mm max.
Surface Resistance: 10^6-$10^9\Omega$
Operating Temperature: -10 ~ +75°C
Storage Temperature: -10 ~ +80°C
Operating Humidity: < 95% RH
Storage Humidity: < 95% RH
Weight of Product: approx. 140g
Core Diameter (tape): 32 mm or 25 mm

ESD Grid Tape

ESD antistatic grid tape uses PET as materials, it features a high-performance adhesive tape for antistatic function, uses in packaging products that are static sensitive and require EMI shielding and can be used for grounding as well. The set contains two rolls of 33 m content each. They can be ordered by Part-No.: 1903EC131.



Technical Specs: Material: PET • Color: transparent + black grid • Rupture elongation factor: 60% • Tensile strength: 4.5 kg/cm^2 • Max. temp.: 80 °C • Surface resistance: 10^6 … 10^9 Ω • Thickness: 0.06 mm • Width: 12 mm • Length on roll: 33 m.

This is a publication by Quadrios GmbH • Bahnhofstraße 16 • D-92670 Windischeschenbach (www.quadrios.de)
All right including translation reserved. Reproduction by any method or the capture in electronic data processing system require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.
All statements without guarantee
© Quadrios GmbH
Version 2026/04