Specifications



Photo is representative



Eaton EP-401737

MTS-40/Z/4 - EP-401737

General specifications	
PRODUCT NAME	Eaton MTS Transfer switch
CATALOG NUMBER	EP-401737
MODEL CODE	MTS-40/Z/4
EAN	4015082973964
PRODUCT LENGTH/DEPTH	93 mm
PRODUCT HEIGHT	93 mm
PRODUCT WIDTH	99 mm
PRODUCT WEIGHT	0.404 kg
COMPLIANCES	RoHS
CERTIFICATIONS	EN IEC 63000:2018

Electrical rating

RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	6 kA
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	15 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	5.5 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
RATED UNINTERRUPTED CURRENT (IU)	40 A

Features & functions

NUMBER OF POLES	4

General information

ACTUATOR TYPE	Short thumb-grip
DEGREE OF PROTECTION (FRONT SIDE)	IP40

Resources

CATALOGUES	eaton-industrial-switch-disconnectors-catalogue-ca008011en-en-gb.pdf Product Range Catalog Industrial switch-disconnectors
DECLARATIONS OF CONFORMITY	eaton-transfer-switch-declaration-of-conformity-eu251508en.pdf
INSTALLATION INSTRUCTIONS	eaton-transfer-switch-mts-16-63-il008079zu.pdf

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2026 Eaton. All Rights Reserved.