

KERN TGC 1K-3

KERN

Slim pocket balance with large stainless steel weighing plate and practical tare pan



Category

Brand	KERN
Product category	Laboratory balance
Product group	Pocket balance
Product family	TGC

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	1000 g
Readability [d]	1 g
Reproducibility	3 g
Linearity	± 6 g
Resolution	1.000
Tare range	1000 g

Adjustment options Adjusting with external weight

Recommended adjusting weight 750 g (M3)

Possible calibration points 1 kg

Stabilization time 2 s

Warm-up time 10 min

Eccentric loading at 1/3 [Max] 3 g

Construction type of the scale Single-range balance

Units	g gn dwt ozt ct oz
-------	-----------------------------------

Weighing capacity [Max] (ct) 5000 ct

Readability carat [d] (ct) 5 ct

Maximum creep (15 minutes) 2 g

Maximum creep (30 minutes) 4 g

Default unit g

Display

Display type	LCD
Display backlight	✓
Display digit height	12 mm
Languages of the user interface	Symbol language

Construction

Dimension housing (W×D×H)	100×130×18 mm
Dimensions weighing surface (Ø)	81 mm
Dimensions weighing surface	81 mm
Material housing	plastic
Material weighing plate	stainless steel
Material display housing	plastic

Functions

IP protection - complete device	-
Auto-off interval(s) in battery mode/rechargeable battery mode	4 min
Tare function	manual (multi)
Number of keys for operation	4

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Li-Metal
Battery	2×CR2032
Battery connection	Pad + Spring
Battery operating time - backlight on	8,75 h
Battery operating time - backlight off	22 h
Battery operating time	8,75 h
Battery capacity	210 mAh
Battery - Number of cells	2
Battery - Individual weight	6 g
Battery - Total weight	12 g
Battery - Construction	Individual cells
Battery capacity (Wh)	0,63 Wh
Battery - Lithium content	110 mg
Battery - Tests passed UN 38.3	✓
Battery/Accu connected	not connected, enclosed

Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	80 %
Humidity of environment [Max]	90 %
Storage temperature [Min]	-20 °C

KERN TGC 1K-3



Slim pocket balance with large stainless steel weighing plate and practical tare pan

Storage temperature [Max] 60 °C

Approval

CE mark ✓

Services (optional)

Article number for adjustment at the location of installation 961-247

Article number for DAkkS calibration 963-127

Article number for certificate of conformity 969-517

Packing & Shipping

Delivery time 1 d

Dimensions packaging (W×D×H) 100×130×16,5 mm

Shipping method Parcel service

Net weight approx. 0,15 kg

Gross weight approx. 0,35 kg

Shipping weight 0,318 kg

Product information

GTIN/EAN number 4045761214255

REACH classification no prohibited substances

Pictograms

STANDARD



OPTION

