

**Tournevis
SDIK PH2**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Tournevis cruciforme isolé VDE, type Phillips, SDIK PH
DIN 7438, ISO 8764/2-PH, emmanchement selon ISO
8764-PH, poignée SoftFinishf

Informations générales de commande

Type	SDIK PH2
Référence	9008580000
Version	Tournevis, longueur de la lame: 100 mm
GTIN (EAN)	4032248056576
Cdt.	1 pièce(s)

**Tournevis
SDIK PH2**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Caractéristiques techniques**Dimensions et poids**

Largeur	220 mm	Largeur (pouces)	8,661 inch
Poids	104 g	Poids net	97 g
Diamètre	36 mm		

Conformité environnementale du produit

REACH SVHC Lead 7439-92-1

Outils à couper

Forme	Philips	Taille	2
longueur de la lame	100 mm		

Classifications

ETIM 3.0	EC001395	ETIM 4.0	EC000174
ETIM 5.0	EC000174	ETIM 6.0	EC000144
UNSPSC	27-11-17-01	eClass 5.1	21-04-04-01
eClass 6.2	21-04-04-01	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.0	21-04-04-06
eClass 9.1	21-04-04-06		

Agréments

Agréments

**Téléchargements**

Agrément/Certificat/Document de conformité	Manufacturer's Declaration - Screwdrivers
Brochure/Catalogue	CAT 4.3 ELECTR 15/16 EN CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN