

KERN 326-06

Individual weight, OIML Class F1, 50 g, Eco Shape, stainless steel polished



Dimensions packaging (W×D×H)	18×18×29 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg

Optional cases

Case - Plastic article number	347-070-400
Case - Aluminium article number	317-060-600
Case - Wood article number	317-060-100

Product information

GTIN/EAN number	4045761223691
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML F1
Product family	326

Measuring System

Test weight - Density uncertainty (kg/m ³)	140
Weight OIML class	F1
Test weight - nominal value	50 g
Permissible tolerance according to OIML (+/-)	0,3 mg
Test weight - Density (kg/m ³)	7950
OIML-compliant	✓
Test weight - Density [Min] (OIML)	7270
Test weight - Density [Max] (OIML)	8890

Construction

Shape weight	Eco Shape
Dimensions (Ø×H)	18×29 mm
Material	stainless steel polished
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-436
Article number for guaranteed plus-deviation	921-436

Packing & Shipping

Delivery time	1 d
---------------	-----