Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2016

Supplier's name or trademark: Miele

Supplier's address: Service, Carl-Miele-Straße 29, 33325 Gütersloh, DE

Model identifier: F 12016 S-2

Type of refrigerating appliance:

Low-noise appliance:	No	Design type:	freestanding
Wine storage appliance:	No	Other refrigerating appliance:	Yes

General product parameters:

Parameter		Value	Parameter	Value
Overal dimensions (millimetre)	Height	851	Total volume (dm³ or l)	102
	Width	553		
	Depth	624		
EEI		100	Energy efficiency class	E
Airborne acoustical noise emissions (dB(A) re 1 pW)		39	Airborne acoustical noise emission class	C
Annual energy consumption (kWh/a)		171,14	Climate class:	extended temperate, temperate, subtropical, tropical
Minimum ambient temperature (ºC), for which the refrigerating appliance is suitable		10	Maximum ambient temperature (ºC), for which the refrigerating appliance is suitable	43
Winter setting		Yes		

Compartment Parameters:

Compartment type		Compartment parameters and values			
		Compartment volume (dm³ or l)	Recommended temperature setting for optimised food storage (ºC) These settings shall not contradict the storage conditions set out in Annex IV, Table 3	Freezing capacity (kg/24h)	Defrosting type (auto-defrost=A, manual defrost=M)
Pantry	No	-	-	-	-
Wine storage	No	-	-	-	-
Cellar	No	-	-	-	-
Fresh food	No	-	-	-	-

Chill	No	-	-	-	-
0-star or ice-making	No	-	-	-	-
1-star	No	-	-	-	-
2-star	No	-	-	-	-
3-star	No	-	-	-	-
4-star	Yes	102,6	-18	6,0	-
2-star section	No	-	-	-	-
Variable temperature compartment	-	-	-	-	-

For 4-star compartments	
Fast freeze facility	Yes
Light source parameters:	
Type of light source	-
Energy efficiency class	-
Minimum duration of the guarantee offered by the manufacturer: 24 months	
Additional information:	
Weblink to the manufacturer's website, where the information in point4(a) Annex of Commission Regulation (EU) 2019/2019 is found: https://www.miele.com/	