Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2016

Supplier's name or trademark: SAWAFUJI - ENGEL

Supplier's address: Fischagasse 44, 2483 Ebreichsdorf, AT

Model identifier: MT35F-G3N-S

Type of refrigerating appliance:

Low-noise appliance:	No	Design type:	freestanding
Wine storage appliance:	No	Other refrigerating appliance:	Yes

General product parameters:

Parameter		Value	Parameter	Value
Overall dimensions (millimetre)	Height	408	Total volume (dm³ or l)	32
	Width	647		
	Depth	364		
EEI		101	Energy efficiency class	F
Airborne acoustical noise emissions (dB(A) re 1 pW)		48	Airborne acoustical noise emission class	D
Annual energy consumption (kWh/a)		80	Climate class:	tropical
Minimum ambient temperature (ºC), for which the refrigerating appliance is suitable		16	Maximum ambient temperature (ºC), for which the refrigerating appliance is suitable	43
Winter setting		No		

Compartment Parameters:

Compartment type		Compartment parameters and values			
		Compartment volume (dm³ or l)	Recommended temperature setting for optimised food storage (ºC) These settings shall not contradict the storage conditions set out in Annex IV, Table 3	Freezing capacity (kg/24h)	Defrosting type (auto-defrost=A, manual defrost=M)
Pantry	No	-	-	-	-
Wine storage	No	-	-	-	-
Cellar	No	-	-	-	-
Fresh food	Yes	-	-	-	-
Chill	No	-	-	-	-
0-star or ice-making	No	-	-	-	-

1-star	No	-	-	-	-
2-star	No	-	-	-	-
3-star	No	-	-	-	-
4-star	No	-	-	-	-
2-star section	No	-	-	-	-
Variable temperature compartment	-	-	-	-	-

Light source parameters:	
Type of light source	-
Energy efficiency class	-
Minimum duration of the guarantee offered by the manufacturer: 36 months	
Additional information:	
Weblink to the manufacturer's website, where the information in point4(a) Annex of Commission Regulation (EU) 2019/2019 is found: http://www.roega.com	