


KERN KFP 300V20M

KERN

Platform: weighing plate of stainless steel, painted steel base, silicone-coated aluminium load cell with protection against dust and water splashes IP65



Category

Brand	KERN
Product category	Component
Product group	Platform
Product family	KFP-V20-IP65

Measuring System

Weighing capacity [Max]	150 kg; 300 kg
Readability [d]	10 g
Minimum weight [Min]	1 kg; 2 kg
Load cell connection	6-wire
Load cell OIML class	C3
Loadcell type	aluminium IP65 silicone-coated

Construction

Dimensions weighing surface (W×D)	650×500 mm
Dimensions weighing surface	650×500 mm
Dimensions weighing platform (W×D×H)	650×500×139 mm
Material weighing plate	stainless steel
Material platform	steel, powder-coated
Material load cell(s)	aluminium
Levelling feet adjustable	✓
Cable length	2,5 m
Allowed cable length display device [Max]	3 m
Platform Construction	Single-Cell
Load cells - number	1

Functions

IP protection - load cell	IP65
---------------------------	------

Approval

Conformity assessment possible ex works	✓
Verification scale interval [e]	50 g; 100 g

Services (optional)

Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	1050×675×250 mm
Shipping method	Parcel service
Net weight approx.	19 kg
Gross weight approx.	26 kg
Shipping weight	35,4 kg

Product information

GTIN/EAN number	4045761250031
REACH classification	no prohibited substances

Pictograms

STANDARD



FACTORY

