

KERN OZL 963



Predefined stereo microscope set with simple telescopic arm and 4.5 W ring illumination unit for greater flexibility at the workstation



Category	
Brand	Optics
Product category	Microscope
Product group	Stereo microscope set
Product family	OZL-9

Construction	
Dimension (W×D×H)	700×255×600 mm
Optical system	Greenough
Tube type	Trinocular
Tube angle of inclination	45°
Tube 360° rotation	✓
Light distribution	0:100
Contrasting methods	Bright field
Interpupillary distance [Min]	55 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	both-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5

Ocular	
Ocular type	Eyepiece HWF 10x / Ø 20mm High Eye Point
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	20 mm
Ocular diameter	30 mm

Objective	
Objectives magnifications	0,7x - 4,5x

Illumination	
Illuminance	Reflected light
Illumination type incident light	LED
Illumination intensity incident light	4,5 W
Illumination dimmable	Incident light

Focussing	
Field of view [Min]	4,4 mm
Field of view [Max]	28,6 mm
Standard total magnification [Min]	7x
Standard total magnification [Max]	45x
Zoom [Min]	0,7x
Zoom [Max]	4,5x
Sample height [Max]	140 mm
Torque regulation	✓
Working distance	100 mm
Magnification ratio	6,4:1
Focusing mechanism	coarse drive

Stereomicroscope stand	
Stand type	universal (telescopic arm with plate)
Diameter mounting microscope head (Ø)	76 mm

Power Supply	
Power supply type	Built-in power supply
	EURO
Plug-in power supply / adapter for countries - optional	AUS
	UK
	US
	CH
Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	100 - 240 V
Power socket for mains adapter	Protective contact plug

Environmental conditions	
Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval	
CE mark	✓

Packing & Shipping	
Delivery time	1 d
Dimensions packaging (W×D×H)	820×420×240 mm

KERN OZL 963



Predefined stereo microscope set with simple telescopic arm and 4.5 W ring illumination unit for greater flexibility at the workstation

Shipping method	Parcel service
Net weight approx.	18 kg
Gross weight approx.	22 kg
Shipping weight	20,5 kg

Product information

GTIN/EAN number	4045761189447
REACH classification	no prohibited substances

Pictograms

STANDARD

