

SAUTER SW 1000

First-class professional Class I, Class II sound level meter



Category

Brand	Sauter
Product category	Environment/ Occupational safety
Product group	Sound level meter
Product family	SW

Measuring System

Sound level meter class	Class 1
Microphone sensitivity	50 mV/Pa
Frequency range [Max]	20 kHz
Sound level [Min] (dB)	20 dB
Sound level [Max] (dB)	134 dB
Frequency range [Min]	10 Hz

Sound level measuring modes	Lp
	Leq
	Ln
	Lcpeak

Sound level methods of evaluation	A
	C
	Z
	B

Units	dB
Readability sound [d] (dB)	0,1 dB

Construction

Dimension housing (W×D×H)	210×80×40 mm
Dimensions device (W×D×H)	300×80×36 mm
Dimensions completely mounted (W×D×H)	340×80×40 mm
Material housing	plastic
Material display housing	plastic

Functions

Limit-setting function	✓
Analogue signal	✓
Hold function	✓
Peak function	✓
Memory function	✓

Power Supply

Supplied power supply	Power supply & battery function (battery not included)
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK
	US
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
	Hz
Power supply cable removable	removable
Input voltage device / power [Max]	12 V, 1 A
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
	mm
Battery / accumulator type	Alkali(-Manganese)
Battery	4×1.5 V AA
Battery connection	Pad + Spring
Battery operating time	10 h

Environmental conditions

Use temperature [Min]	-10 °C
Use temperature [Max]	50 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-281
Article number for factory calibration	961-281

SAUTER SW 1000



First-class professional Class I, Class II sound level meter

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	405×305×100 mm
Shipping method	Parcel service
Net weight approx.	0,40 kg
Gross weight approx.	1,4 kg
Shipping weight	2,5 kg

Product information

GTIN/EAN number	404576 1200845
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

