

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013

| INFORMATION                                                                   |                | Value         | Unit            |
|-------------------------------------------------------------------------------|----------------|---------------|-----------------|
| 1. Supplier name or trademark                                                 |                | DELL          |                 |
| 2. Model identifier                                                           |                | P2421DC       |                 |
| 3. Energy Efficiency Class for standard Dynamic Range (SDR)                   |                | E             |                 |
| 4. On mode power demand for Standard Dynamic Range (SDR)                      |                | 18.5          | W               |
| 5. Energy Efficiency Class for standard Dynamic Range (HDR)                   |                |               |                 |
| 6. On mode power demand in High Dynamic Range (HDR) mode                      |                |               | W               |
| 7. Off mode, power demand                                                     |                | 0.2           | W               |
| 8. Standby mode power demand                                                  |                | 0.3           | W               |
| 9. Networked standby mode power demand                                        |                |               | W               |
| 10. Electronic display category                                               |                | Monitor       |                 |
| 11. Size ratio                                                                |                | 16 : 9        |                 |
| 12. Screen resolution (pixels)                                                |                | 2560 x 1440   | pixels          |
| 13. Screen diagonal                                                           |                | 60.5          | cm              |
| 14. Screen diagonal                                                           |                | 24            | inches          |
| 15. Visible screen area                                                       |                | 1561.4        | cm <sup>2</sup> |
| 16. Panel technology used                                                     |                | LED LCD       |                 |
| 17. Automatic Brightness Control (ABC) available                              |                | No            |                 |
| 18. Voice recognition sensor available                                        |                | No            |                 |
| 19. Room presence sensor available                                            |                | No            |                 |
| 20. Image refresh frequency rate                                              |                | 60            | Hz              |
| 21. Minimum guaranteed availability of software and firmware updates (until): |                | 21 07 2032    |                 |
| 22. Minimum guaranteed availability of spare parts (until)                    |                | 21 07 2031    |                 |
| 23. Minimum guaranteed product support (until)                                |                | 21 10 2031    |                 |
| 24. Power supply type:                                                        |                | Internal      |                 |
| i External standardised power supply (included in the product box)            | Standard name  |               |                 |
|                                                                               | Input voltage  |               | V               |
|                                                                               | Output voltage |               | V               |
| ii External standardised suitable power                                       |                | Standard name |                 |

| INFORMATION                                 |                            | Value | Unit |
|---------------------------------------------|----------------------------|-------|------|
| supply (if not included in the product box) |                            |       |      |
|                                             | Required output voltage    |       | V    |
|                                             | Required delivered current |       | A    |
|                                             | Required current frequency |       | Hz   |