

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013 with regard to energy labelling of electronic displays

	Parameter	Parameter or value and precision			Unit
1.	Supplier's name or trademark.	MINIX			
	Supplier's address.	Smart Import Solutions, Plattenborgtsraat 20, 8043 TT Zwolle NETHERLANDS			
2.	Model identifier	SF15 FOLD			
3.	Energy Efficiency Class for Standard Dynamic Range (SDR)	D			
4.	On mode power demand in SDR	11,0			W
5.	Energy Efficiency Class for High Dynamic Range (HDR)	F			
6.	On mode power demand in HDR, if implemented	17,3			W
7.	Off mode, power demand, if applicable	n.a.			W
8.	Standby mode power demand, if applicable	0,4			W
9.	Networked standby mode power demand, if applicable	n.a.			W
10.	Electronic display category	Monitor			
11.	Size ratio	16	:	9	
12.	Screen resolution	1 920	x	1 080	pixels
13.	Screen diagonal	39,5			cm
14.	Screen diagonal	16			inches
15.	Visible screen area	13,4			dm²
16.	Panel technology used	LED LCD			
17.	Automatic Brightness Control (ABC) available	No			
18.	Voice recognition sensor available	No			
19.	Room presence sensor available	No			
20.	Image refresh frequency rate (default)	60			Hz
21.	Minimum guaranteed availability of software and firmware updates (from the date of end of the placement on the market)	2			Years
22.	Minimum guaranteed availability of spare parts (from the date of end of the placement on the market)	2			Years
23.	Minimum guaranteed product support	2			Years
	Minimum duration of the general guarantee offered by the supplier	2			Years
24.	Power supply type	External			
25.	External power supply (non standardized and included in the product box)				
	i	PD 30W charger			
	ii	Input voltage	240		V

	<i>iii</i>	Output voltage	20,0	V
26.	External standardised power supply (or suitable one if not included in the product box)			
	<i>i</i>	-		
	<i>ii</i>	Required output voltage	-	V
	<i>iii</i>	Required delivered current (minimum)	-	A
	<i>iv</i>	Required current frequency	-	Hz

Model placed on the Union market from 10/04/2025



EPREL registration number: 2314359

<https://eprel.ec.europa.eu/qr/2314359>

Supplier: Smart Import Solutions (Importer)

Website: www.pepper-jobs.eu

Customer care service:

Name: Smart Import Solutions

Website: <https://www.pepper-jobs.eu/nl/>

Email: richard@smartimportsolutions.nl

Phone: +31629557135

Address:

Plattenborgtsraat 20, 8043 TT Zwolle NETHERLANDS