Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013 with regard to energy labelling of electronic displays

	Parameter	Parameter or value and precision	Unit
1.	Supplier's name or trademark.	JAPANNEXT	
	Supplier's address.	Customer Service, Rue Réaumur 124, 75002 Paris EE, FR	
2.	Model identifier	JN-IPS238FHDR-C65W-HSP	
3.	Energy Efficiency Class for Standard Dynamic Range (SDR)	E	
4.	On mode power demand in SDR	18,0	W
5.	Energy Efficiency Class for High Dynamic Range (HDR)	G	
6.	On mode power demand in HDR, if implemented	26,0	W
7.	Off mode, power demand, if applicable	n.a.	W
8.	Standby mode power demand, if applicable	0,4	W
9.	Networked standby mode power demand, if applicable	n.a.	W
10.	Electronic display category	Monitor	
11.	Size ratio	16 : 9	
12.	Screen resolution	1 920 x 1 080	pixels
13.	Screen diagonal	61,0	cm
14.	Screen diagonal	23	inches
15.	Visible screen area	15,6	dm^2
16.	Panel technology used	LED LCD	
17.	Automatic Brightness Control (ABC) available	No	
18.	Voice recognition sensor available	No	
19.	Room presence sensor available	No	
20.	Image refresh frequency rate (default)	60	Hz
21.	Minimum guaranteed availability of software and firmware updates (from the date of end of the placement on the market)	8	Years
22.	Minimum guaranteed availability of spare parts (from the date of end of the placement on the market)	8	Years
23.	Minimum guaranteed product support	8	Years
	Minimum duration of the general guarantee offered by the supplier	2	Years
24.	Power supply type	Internal	
25.	External power supply (non standardized and included in the product box)		
	i -		
	ii Input voltage	-	V

	iii	Output voltage	-	V
26.	External standardised power supply (or suitable one if not included in the product box)			
	i	-		
	ii	Required output voltage	-	V
	iii	Required delivered current (minimum)	-	A
	iv	Required current frequency	-	Hz

Model placed on the Union market from 27/03/2024

EPREL registration number: 1874264

https://eprel.ec.europa.eu/qr/1874264

Supplier: JAPANNEXT EUROPE (Importer)

Website: www.eu.japannext.com

Customer care service:

Name: Customer Service

Website: www.japannext.eu

Email: contact@japannext.com

Phone: +33970708090

Address:
Rue Réaumur 124
75002 Paris
France