

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013

INFORMATION		Value	Unit
1. Supplier name or trademark		LG Electronics	
2. Model identifier		32GK650F	
3. Energy Efficiency Class for standard Dynamic Range (SDR)		G	
4. On mode power demand for Standard Dynamic Range (SDR)		37.8	W
5. Energy Efficiency Class for standard Dynamic Range (HDR)			
6. On mode power demand in High Dynamic Range (HDR) mode			W
7. Off mode, power demand		0.3	W
8. Standby mode power demand		0.5	W
9. Networked standby mode power demand			W
10. Electronic display category		Monitor	
11. Size ratio		16 : 9	
12. Screen resolution (pixels)		2560 x 1440	pixels
13. Screen diagonal		80	cm
14. Screen diagonal		31	inches
15. Visible screen area		2735.4	cm ²
16. Panel technology used		LED LCD	
17. Automatic Brightness Control (ABC) available		No	
18. Voice recognition sensor available		No	
19. Room presence sensor available		No	
20. Image refresh frequency rate		50	Hz
21. Minimum guaranteed availability of software and firmware updates (until):			
22. Minimum guaranteed availability of spare parts (until)			
23. Minimum guaranteed product support (until)			
24. Power supply type:		External	
i External standardised power supply (included in the product box)	Standard name		
	Input voltage		V
	Output voltage		V
ii External standardised suitable power supply (if not included in the product box)	Standard name		
	Required output voltage		V
	Required delivered current		A
	Required current frequency		Hz