



AOC E2 22E2UMF LED display 54,6 cm (21.5") 1920 x 1080 Pixel Full HD Nero

Marchio : AOC

Famiglia del prodotto: E2

Codice prodotto: 22E2UMF

Nome del prodotto : 22E2UMF

Screen size (inch) 21.5, Panel resolution 1920x1080, Max Refresh rate 75 Hz, Panel type VA, HDMI HDMI 1.4 x 1, DisplayPort DisplayPort 1.2 x 1, D-SUB (VGA) 1x, Sync technology (VRR) Adaptive Sync

[AOC E2 22E2UMF LED display 54,6 cm \(21.5"\) 1920 x 1080 Pixel Full HD Nero:](#)

Monitor FHD ad alte prestazioni da 21,5": Rivoluziona il tuo spazio di lavoro

22E2UMF presenta un monitor da 21,5 pollici progettato per rivoluzionare il tuo spazio di lavoro. Con un supporto regolabile in altezza che garantisce comfort ergonomico, un design senza cornice su tre lati per un'esperienza visiva coinvolgente e potenti altoparlanti da 2W, questo monitor combina stile e funzionalità in modo impeccabile. L'USB HUB integrato facilita la connettività per le tue periferiche, ottimizzando il tuo flusso di lavoro. Inoltre, grazie alla tecnologia flicker free, riduci l'affaticamento degli occhi durante un utilizzo prolungato del monitor. Aumenta la tua produttività con il 22E2UMF.



Display		Ports & interfaces	
Display diagonal *	54.6 cm (21.5")	HDCP version	1.4
Display resolution *	1920 x 1080 pixels	AC (power) in	✓
HD type *	Full HD	Ergonomics	
Native aspect ratio *	16:9	VESA mounting *	✓
Display technology *	LED	Panel mounting interface	100 x 100 mm
Panel type *	VA	Cable management	✓
LED backlight	✓	Cable lock slot *	✓
Backlight type	W-LED	Cable lock slot type	Kensington
Touchscreen *	✗	Height adjustment *	✓
Screen shape *	Flat	Adjustable height (max)	15 cm
Contrast ratio (typical) *	3000:1	Pivot	✓
Contrast ratio (dynamic)	20000000:1	Pivot angle	-90 - 90°
Maximum refresh rate *	75 Hz	Swivelling	✓
Viewing angle, horizontal	178°	Swivel angle range	0 - 175°
Viewing angle, vertical	178°	Tilt adjustment	✓
Display number of colours *	16.7 million colours	Tilt angle range	-5 - 35°
Digital horizontal frequency	30 - 85 kHz	Power	
Digital vertical frequency	48 - 75 Hz	Energy efficiency class (SDR) *	D
High Dynamic Range (HDR) supported	✓	Energy efficiency class (HDR) *	E
sRGB coverage (typical)	100.9%	Energy consumption (SDR) per 1000 hours *	12 kWh
NTSC coverage (typical)	72%	Energy consumption (HDR) per 1000 hours *	15 kWh
Performance		Power consumption (typical) *	15 W
VESA Adaptive Sync support	✓	Power consumption (standby) *	0.5 W
Flicker-free technology	✓	Power consumption (off)	0.3 W
Multimedia		AC input voltage	100 - 240 V
Number of speakers	2	AC input frequency	50/60 Hz
RMS rated power	4 W		

Multimedia		Power	
Built-in speaker(s) *	✓	Power supply type	Internal
Built-in camera *	✗	Energy efficiency scale	A to G
Design		Weight & dimensions	
Market positioning *	Office	Width (with stand)	492.1 mm
Product colour *	Black	Depth (with stand)	200.1 mm
Frameless design	✓	Height (with stand)	386.1 mm
Front bezel colour	Black	Weight (with stand)	4.39 kg
Detachable stand	✓	Width (without stand)	492.1 mm
Feet colour	Black	Depth (without stand)	51.1 mm
		Height (without stand)	290.2 mm
		Weight (without stand)	2.63 kg
Ports & interfaces		Packaging data	
Built-in USB hub *	✓	Package width	559 mm
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Package depth	127 mm
USB upstream port type	USB Type-B	Package height	520 mm
Number of upstream ports	1	Package weight	6.69 kg
USB Type-A downstream ports quantity	4		
VGA (D-Sub) ports quantity	1	Packaging content	
HDMI *	✓	Stand included	✓
HDMI ports quantity	1		
HDMI version	1.4	Sustainability	
DisplayPorts quantity	1	Sustainability compliance	✓
DisplayPort version	1.2	Sustainability certificates	EPEAT Gold, TCO
Audio input	✓		
Headphone out *	✓	Other features	
Headphone outputs	1	Local dimming	✓
Headphone connectivity	3.5 mm	Mean time between failures (MTBF)	70000 h
HDCP	✓		



4038986122092

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 09-MAR-2025. Prints or copies of Information are only valid on the printed Publication date