

Maße	M 8	M 10	M 12	M 16
d_k	16,55	19,65	24,65	30,65
k	6,38	7,45	9,65	11,75
g	3	3,2	3,6	4,2
b_1	22	26	30	38
b_2	28	32	36	44
b_3	-	-	-	57

