

Kemo[®]

Electronic

M032S

UNIVERSAL AMPLIFIER 12 W "PLUG & PLAY"

UNIVERSAL VERSTÄRKER 12 W "PLUG & PLAY"



Deutsch



English



Español



Français



Nederlands



Русский



PLUG & PLAY



Brilliant output signal!

M032S | Universal Verstärker 12 W "Plug & Play"

Verstärkermodul mit Buchsen für den Signaleingang und für die Stromversorgung. Eingebauter Lautstärkereglер, Lautsprecheranschluss über Kabel.

Technische Daten:

Betriebsspannung: 6 - 16 V/DC | **Stromaufnahme:** max. 800 mA | **Eingangsempfindlichkeit:** < 80 mV | **Lautsprecheranschluss:** 4 - 16 Ohm | **Musikleistung:** max. 12 W bei 16 V an einem 4 Ohm Lautsprecher | **Frequenzgang:** ca. 40 - 20.000 Hz | **Stromversorgungsbuchse:** für Netzstecker 2,5 mm

M032S | Universal Amplifier 12 W "Plug & Play"

Amplifying module with jacks used for the signal input and for the power supply. Inserted loudspeaker regulator and loudspeaker connection are over the cables.

Technical data:

Operating voltage: 6 - 16 V/DC | **Current consumption:** max. 800 mA | **Input sensitivity:** < 80 mV | **Loudspeaker connection:** 4 - 16 ohm | **Music power:** max. 12 W with 16 V at a 4 ohm loudspeaker | **Frequency response:** approx. 40 - 20.000 Hz | **Power supply jack:** for mains plug 2.5 mm

E Amplificador Universal 12 W "Plug & Play" | **F** Amplificateur universel 12 W "Plug & Play" | **NL** Universeel versterker 12 W "Plug & Play" | **RUS** Универсальный усилитель 12 Ватт "Plug & Play"



Available accessory / Lieferbares Zubehör:

M040N Universal-Vorverstärker /

M040N Universal preamplifier

www.kemo-electronic.de



191512
A26JN



Dimensions:
approx. 72 x 50 x 42 mm
(without fixing straps)

P / Module / M032S / Ver.1.0 / KV008