





MODEL	VOLTAGE		NO LOAD		AT MAXIMUM EFFICIENCY				STARTING		max. OUTPUT POWER W	POLES	CAPACITOR	BRUSHES	REDUCTION RATIO
	Operating Range	Nominal	Speed	Current	Speed	Current	Torque	Output Power	Current	Torque					
	VDC	VDC	rpm	A	rpm	A	mNm	W	A	mNm					
GM12F-N20VS-09190/298-R	1,0-1,5	1,0	10	0,03	7	0,07	3,22	0,02	0,17	107,30	0,03	3	none	metal	298 : 1



DIRECTION OF ROTATION



Irrtum und Druckfehler vorbehalten / Errors and Omissions excepted