

## D Datenblatt

**PA-Lautsprecherchassis 20,86 cm (8")**

Best.-Nr. 300842

**Technische Daten**

Lautsprechergröße .....	20,86 cm (8")
Belastbarkeit (RMS) .....	100 W
Belastbarkeit (max.) .....	300 W
Impedanz .....	8 Ω
Frequenzbereich .....	70 – 5000 Hz
Schalldruckpegel .....	96 dB
Einbau-Ø .....	179 mm
Einbautiefe .....	94 mm
Gewicht .....	3 kg

## GB Data sheet

**PA loudspeaker chassis 20.86 cm (8")**

Item no. 300842

**Technical data**

Speaker size .....	20.86 cm (8")
Load capacity (RMS) .....	100 W
Load capacity (max.) .....	300 W
Impedance .....	8 Ω
Frequency range .....	70 – 5000 Hz
Sound pressure level .....	96 dB
Installation Ø .....	179 mm
Installation depth .....	94 mm
Weight .....	3 kg

Dies ist eine Publikation der Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau ([www.conrad.com](http://www.conrad.com)).

Alle Rechte einschließlich Übersetzung vorbehalten. Reproduktionen jeder Art, z. B. Fotokopie, Mikroverfilmung, oder die Erfassung in elektronischen Datenverarbeitungsanlagen, bedürfen der schriftlichen Genehmigung des Herausgebers. Nachdruck, auch auszugsweise, verboten. Die Publikation entspricht dem technischen Stand bei Drucklegung.

Copyright 2018 by Conrad Electronic SE.

\*300842\_v4\_0318\_02\_IPL\_ds

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau ([www.conrad.com](http://www.conrad.com)).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2018 by Conrad Electronic SE.

\*300842\_v4\_0318\_02\_IPL\_ds