





HP Coated Paper



The HP Designjet printing system—the complete solution

HP DesignJet printers, Original HP inks and printheads, Original HP printing materials and HP Scitex printers, are designed to work together as a system to provide reliable, consistent results with every print.



Create presentation-quality images

Accomplish more with consistent results

From line drawings to illustrations and light ink-density graphics, see high-quality, consistent image quality print to print and roll to roll.

Improve your response time

Handle prints with confidence right off the printer. An enhanced coating provides ink abrasion resistance to help you deliver on quick turnaround times.

Do more, with the environment in mind

Gain versatility with this premium bright white paper. From working comps and design proofs to fine line drawings and illustrations, meet the project needs and the environmental objectives of your company and clients with a PEFC™-certified paper.

Target customers	Applications	Benefits
Architects	Posters and presentations	Crisp text and graphics, consistent high-quality results
Engineers	POP and retail displays	Resistance to ink abrasion for easy handling
Geographic Information Systems (GIS) professionals	Geographic Information Systems (GIS)	Broad HP Designjet printer compatibility ¹
Graphic designers	Architecture (AEC) Engineering (MCAD)	PEFC™-certified paper
Print service providers		Recyclable through commonly available programs

¹ Requires 2-inch spindle for compatibility with the HP Designjet L25500 and L26500 Printer series.

Technical specifications



HP Coated Paper

For the latest ICC profiles/paper presets and a variety of resources to help you get the most out of your printer and HP large format printing materials, please visit HPLFMedia.com.

Weight	90 g/m ² per ISO 536 Test Method, (24 lbs)			
Thickness	114 microns/4.5 mil per ISO 534 Test Method			
Opacity	93% per TAPPI T-425 Test Method			
Brightness	89% per TAPPI T-452 Test Method			
Whiteness	145 per CIE Whiteness ISO 11475 D65/10° Outdoor Daylight Test Method			
Finish	Matte			
Operating temperature	15 to 35° C / 59 to 95° F			
Operating humidity	20 to 80% RH			
Dry time	Immediate (at 23° C, 50% RH)			
Lamination	Yes, with commercially available thermal and pressure-sensitive laminate films			
Shelf life	2 years, unopened in original packaging			
Storage temperature	0 to 40° C / 32 to 104° F			
Storage humidity	5 to 95% RH			
Recyclability	Recyclable through commonly available recycling programs			
Country of origin	Product of Germany			
Ordering information	Product numbers	Roll sizes	UPC Codes	Region
	C6019B ¹	610 mm x 45,7 m (24 in x 150 ft)	848412012750	Worldwide
	C6020B ¹	914 mm x 45,7 m (36 in x 150 ft)	848412012774	Worldwide
	C6567B ¹	1067 mm x 45,7 m (42 in x 150 ft)	848412012798	Worldwide
	C6568B ¹	1372 mm x 45,7 m (54 in x 150 ft)	848412012804	Worldwide
	C6980A ¹	914 mm x 91,4 m (36 in x 300 ft)	848412012781	Worldwide
	Q1443A	(A2) 420 mm x 45,7 m	848412014143	Japan
	Q1442A	(A1) 594 mm x 45,7 m	848412014150	Europe, Singapore
	Q1441A	(A0) 841 mm x 45,7 m	848412012767	Japan, Europe
Warranty	HP large format printing materials are free from defects in materials and workmanship. For warranty statement please see HPLFMedia.com/hp/MediaWarranties .			

¹ Requires 2-inch spindle for compatibility with the Latex 260.



For detailed information on the HP large format print media portfolio and to order, visit HPLFMedia.com

© 2015 Hewlett-Packard Development Company. © 2015 Brand Management Group. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP and BMG shall not be liable for technical or editorial errors or omissions contained herein.

HP is a registered trademark of Hewlett-Packard Company and is used by Brand Management Group on license from Hewlett-Packard Company.

