

FINO+ X24

LED TV DVD/DVB-T



FINO
S E R I E S
LED TV 24
BACKLIGHT



**FULL
HD**
1080P

- 60 cm (23,6") LED Backlight Panel
- Integrated DVB-T Tuner & Slot-In Type DVD Player
- Full-HD 1.080p
- 2x HDMI – Input with HDCP Support
- YPbPr Component Input
- TV-Function
- PC-Monitor
- USB Input for Playback of Multimedia Files
- DVD, DVD±R, DVD±RW, CD, CD-R, CD-RW, MP3, JPEG Picture CD,...
- Hotel Mode

Technische Daten / Specifications		
Bildschirmgröße / Screen Size (Diagonal)	60cm (23,6")	
Bildschirmformat / Screen Format	16:9	
Auflösung / Resolution	1.920 x 1.080	
Helligkeit / Brightness	300 cd/m ²	
Kontraste / Contrast Ratio	1.000:1	
Blickwinkel / Viewing Angle	170° (H) / 160° (V)	
Reaktionszeit / Reaction Time	5ms	
Analog TV / Analogue TV	Video System	PAL, SECAM
	Audio System	B/G, D/K, I, L/L'
	Max. Senderspeicher / Max. Storage Channels	400
Digital TV (DVB-T)	Modulation	COFDM 2k/8k, QPSK, 16QAM/64QAM
	Sound System	MPEG-1/2 Layer 1, 2, 3
	Video System	MPEG-2
	Funktionen / Functions	Elektronischer Programmführer (EPG), Videotext, Untertitel, ... Electric Program Guide (EPG); Teletext, Subtitle,...
DVD Wiedergabeformate / DVD Reply Formats	DVD, DVD±R, DVD±RW, CD, CD-R, CD-RW, MP3, JPEG Picture CD,...	
HDMI Spezifikationen / HDMI Specifications	480p, 576p, 720p, 1080i, 1080p	
Bildeinstellungen / Picture Settings	Standard, Benutzerdefiniert, Dynamisch, Mild Standard, User, Dynamic, Mild	
Audioeinstellungen / Audio Settings	Standard, Benutzerdefiniert, Film, Musik, Sport Standard, User, Movie, Music, Sport	
Wandhalterung / Wall Mounting Support	100 mm Lochabstand (nicht im Lieferumfang) 100 mm distance (not included)	
Lautsprecher-Ausgang / Speakers-Output	2 x 3W	
Anschlüsse /	2x HDMI Eingang, 75 Ohm Antennenanschluss, A/V Eingang, YPbPr Komponenteneingang, VGA-Eingang,	

Fino+ X24



www.odys.de
MADE TO ENTERTAIN

Connections	Mini-Scartanschluss, USB-Anschluss 2x HDMI Input, 75 Ohm Antenna, A/V In, YPbPr Composite In, VGA Input, Mini-Scart Input, USB- Connector
Stromversorgung / Power Supply	Eingang: AC100-240V, 50/60Hz, Ausgang: 12V, 3A Input: AC100-240V, 50/60Hz, Output: 12V, 3A
Stromverbrauch / Power Consumption	≤ 35W, Stand-by: ≤ 1W
Gewicht / Weight	~ 4,5 kg
Abmessung (ohne Standfuss) / Dimension (without Stand)	572 x 38 x 373 [mm]
Abmessung (mit Standfuss) / Dimension (with Stand)	572 x 145 x 414 [mm]
Lieferumfang / Package Content	Fino+ X24, Stromadapter, Mini Scart-Adapter, Fernbedienung (incl. Batterie), Anleitung Fino+ X24, Power Adapter, Mini Scart Adapter, Remote Control (incl. Battery), Manual

