

**Z-series
ZAP/TW ZIA1.5/4L**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Signal wiring**

Tailored and particularly compact: with our AIO initiator/actuator terminal blocks, you are relying on an application-optimised solution for signal wiring. We also offer you other terminal blocks featuring spring and screw connection technology for signal wiring.

General ordering data

Type	ZAP/TW ZIA1.5/4L
Order No.	1649550000
Version	Z-series, End plate, Separation plate
GTIN (EAN)	4008190295172
Qty.	50 pc(s).

Data sheet

Z-series ZAP/TW ZIA1.5/4L

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	5.08 mm	Width (inches)	0.2 inch
Height	81 mm	Height (inches)	3.189 inch
Depth	45.8 mm	Depth (inches)	1.803 inch
Net weight	6.057 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	End and intermediate plate	Rail	TS 35
---------	----------------------------	------	-------

Additional technical data

Installation advice	Direct mounting	Snap-on	Yes
Type of fixing	Top-hat rail 35 mm		

Dimensions

TS 35 offset	54 mm
--------------	-------

Classifications

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
UNSPSC	30-21-18-27	eClass 5.1	27-14-11-33
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-33		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN.WSCAD
Engineering Data	STEP