



### Lichtmangel ausgleichen: Wohlfühlen im Winter

Im Herbst und Winter kann es zu Lichtmangelercheinungen kommen. Oft werden diese Störungen des Hormonhaushalts als Winterdepression bezeichnet. Symptome sind:

- Unausgeglichenheit
- gedrückte Stimmung
- Energie- und Antriebslosigkeit
- allgemeines Unwohlsein

Künstliches Licht kann dies nicht ausgleichen. Das spezielle, helle Licht der Tageslichtlampe kann als Lichtdusche - ohne Medikamente - auf den Hormonhaushalt einwirken und vorbeugend oder behandelnd eingesetzt werden.

### Balancing shortage of light: Well-Being in winter

In winter, there may be light deficiency (disturbance of the hormone-budget):

- imbalance
- depressed mood
- less energy and motivation
- general malaise

Artificial light can not compensate.

The special, bright light of daylight lamp can influence - without medicine - the hormone budget and preventive or treated used.

german|engineering

## TL 90 Tageslichtlampe

Lichtdusche mit Tageslicht  
- zur Anwendung bei Lichtmangelercheinungen

Besonders attraktives Design

Simulation von Sonnenlicht:

Lichtstärke ca. 10.000 Lux  
(bei 15 - 20 cm Abstand)

Behandlungszeit-Anzeige in 15-Min-Schritten (8 LEDs)

Besonders helle und gleichmäßige Ausleuchtung

Flackerfreie Zündung - sofort angenehmes Licht ohne Stroboskopeffekte

Flimmerfrei und UV-frei

Energiesparendes Leuchtmittel

Stufenlose Neigungsverstellung mit stabilem Standfuß

Komfortable Ein-Knopf-Bedienung

Zertifiziertes Medizinprodukt

2 x 36 Watt Röhre

Wirkungsgrad des Vorschaltgerätes: ~ 98%

Wirkungsgrad der Lampe: 64 lm/W

Farbtemperatur der Leuchtröhren: 6.500 Kelvin

Produktmaße: 581 x 337 x 241 mm

Standfläche: 292 x 241 x 117 mm

Leuchtschirm: 513,6 x 337 mm

Produktgewicht: ca. 3 kg

3 Jahre Garantie

VE: 2 / Transportkarton: -

EAN-Nr.: 4211125 60830 9

Art.-Nr.: 608.30

## TL 90 Brightlight

Light box with daylight  
- For use in case of light deprivation

Exceptionally attractive design

Simulation of sunlight:

Intensity of light approx. 10.000 Lux  
(at a distance of 15 - 20 cm)

Treatment time indicator in 15-min-steps (8 LEDs)

Exceptionally bright and even illumination

Flicker-free starting - immediately pleasant light without stroboscopic effects

Flicker-free and UV-free

Energy-saving light source

Continuously adjustable inclination with stable stand

Convenient one-button operation

Certified medical product

2 x 36 Watt tube

Degree of efficiency of the ballast: ~ 98%

Source efficiency of the bulb: 64 lm/W

Color temperature of tubes: 6.500 Kelvin

Product measurements: 581 x 337 x 241 mm

Base measurements: 292 x 241 x 117 mm

Illumination surface: 513.6 x 337 mm

Product weight: approx. 3 kg

3 year guarantee

Sales unit: 2 / Shipping carton: -

EAN no.: 4211125 60830 9

Item no.: 608.30