



Wolfcraft GmbH
Wolfstraße 1
56746 Kempenich
Germany
info@wolfcraft.com
www.wolfcraft.com



max.
80 m/sec
13.300 rpm

EN
13236

X27 - 1694 000

1694 000



wolfcraft®

PRO ★★★★★

TURBO



Ø 115 mm

