

wolcraft®



2133000

140002133 Y16 - 2133000

INFO +



EN
1083-2



max.
RPM
4.500



max.
RPM
4.500



max.
RPM
4.500



max.
RPM
1.000



Raccolta differenziata.
Verifica le disposizioni
del tuo Comune



4 006885 213302

wolcraft GmbH
Wolffstraße 1
56746 Kempenich
Germany
info@wolcraft.com
www.wolcraft.com



Ø 25 mm



Ø 75 mm



Ø 75 mm

Ø 28 mm